



DOOR PULLS • PUSH BARS

# SWINGING DOOR

HARDWARE

## OFFSET DOOR PULL PH-4000

- 1" Diameter Solid Aluminum Round
- 3-1/4" Offset
- Projection 3-1/4"
- Door Clearance 2-1/4"
- CTC 9", 10" and 12"
- Anodized Finishes AL, DU (Storefront Bronze), and BK
- Other Finishes Available on Request
- Mounting Hardware Include



SPECIFY: Length, Finish & Mounting Hardware (T1 or T6)

## OFFSET PULL SET PH-4000-2

- 1" Diameter Solid Aluminum Round
- 3-1/4" Offset
- Projection 3-1/4"
- Door Clearance 2-1/4"
- CTC 9", 10" and 12"
- Anodized Finishes AL, DU (Storefront Bronze), and BK
- Other Finishes Available on Request
- Mounting Hardware Included (T5)

SPECIFY: Length and Finish

## OFFSET PULL & SINGLE BEND PUSH BAR SET PP-1000

- 1" Diameter Solid Aluminum Round
- Projection: See Pull/Push Specifications
- CTC: See Pull/Push Specifications
- Anodized Finishes AL, DU, and BK
- Other Finishes Available on Request
- Mounting Hardware Included

SPECIFY: Length, Finish & Mounting Hardware



## OFFSET PULL & DOUBLE BEND PUSH BAR SET

- 1" Diameter Solid Aluminum Round
- Projection: See Pull/Push Specifications
- CTC: See Pull/Push Specifications
- Anodized Finishes AL, DU, and BK
- Other Finishes Available on Request
- Mounting Hardware Included

SPECIFY: Length , Finish & Mounting Hardware



## SINGLE BEND PUSH BAR PB-1000 DOUBLE BEND PUSH BAR PB-2000

- 1" Diameter Solid Aluminum Round
- Projection 2-1/4" with 1-1/4" Door Clearance
- CTC 33-1/16", 39-1/16" and 45-1/16"
- Anodized Finishes AL, DU, and BK
- Other Finishes Available on Request
- Mounting Hardware Included

SPECIFY: Length, Finish & Mounting Hardware (T1 or T6)



## MOUNTING HARDWARE FOR VARIOUS COMBINATIONS

Single Push/Pull: Specify either T1 Thru Bolt, or T6 Concealed Mount

Push/Pull Sets: Back to Back at Bottom of Pull, Thru Bolts on free ends

**International Door Closers, Inc.**

COPYRIGHT 2014 INTERNATIONAL DOOR CLOSERS, INC

**West: 800-544-4422 • East: 800-225-6737**

**www.intldoorclosers.com**