

LBB 9082/00 Unidirectional Gooseneck Microphone

www.boschsecurity.com



BOSCH

Invented for life



- ▶ Unidirectional dynamic microphone
- ▶ Flexible stem
- ▶ Excellent speech reproduction
- ▶ Rugged construction
- ▶ Built-in pop shield

The gooseneck microphone is a stylish high quality unidirectional dynamic microphone, mainly intended for public address applications.


Functions

The flexible stem has an M10 screw fitting for mounting onto (fireman's) panels, lecterns or desktops.


Certifications and approvals

Region	Certification
Europe	CE


Installation/configuration notes



Dimensions in mm



Circuit diagram



Frequency response

Technical specifications

Electrical*

Type	Gooseneck
Polar pattern	Unidirectional
Frequency response	100 Hz to 15 kHz
Sensitivity	1.2 mV/Pa $\pm$ 4 dB
Rated output impedance	500 ohm

* Technical performance data acc. to IEC 60268-4

Mechanical

Dimensions	28 x 385 mm (1.10 x 15.16 in)
Weight	225 g (8 oz)
Color	Black
Cable type	2-core screened
Cable length	230 mm

Environmental

Operating temperature	-25 °C to +55 °C (-13 °F to +131 °F)
Storage temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative humidity	<95%

Ordering information

LBB 9082/00 Unidirectional Gooseneck Microphone

Dynamic gooseneck microphone, unidirectional, matt-black finish, flexible stem, flange mounting, 230 mm, 2-core screened connection cable.

Order number **LBB9082/00**

Represented by:

Americas:

Bosch Security Systems, Inc.
12000 Portland Avenue South
Burnsville MN 55337, USA
Phone: +1-800-392-3497
Fax: +1-800-955-6831
audiosupport@us.bosch.com
www.boschsecurity.com

Europe, Middle East, Africa:

Bosch Security Systems B.V.
P.O. Box 80002
5617 BA Eindhoven, The Netherlands
Phone: +31 40 2577 284
Fax: +31 40 2577 330
emea.securitysystems@bosch.com
www.boschsecurity.com

Asia-Pacific:

Robert Bosch (SEA) Pte Ltd, Security Systems
11 Bishan Street 21
Singapore 573943
Phone: +65 6571 2808
Fax: +65 6571 2699
apr.securitysystems@bosch.com
www.boschsecurity.asia

China:

Bosch (Shanghai) Security Systems Ltd.
201 Building, No. 333 Fuquan Road
North IBP
Changning District, Shanghai
200335 China
Phone +86 21 22181111
Fax: +86 21 22182398
www.boschsecurity.com.cn

America Latina:

Robert Bosch Ltda Security Systems Division
Via Anhanguera, Km 98
CEP 13065-900
Campinas, Sao Paulo, Brazil
Phone: +55 19 2103 2860
Fax: +55 19 2103 2862
latam.boschsecurity@bosch.com
www.boschsecurity.com