



# PD10-UL-M-KIT

- PTS "PUSH TO SET" TECHNOLOGY
- HIGH OUTPUT MODE FOR TALL VERTICAL ROD DOORS
- ELECTRONIC DOGGING
- WORKS ON DOROMATIC, FALCON, & FIRST CHOICE DEVICES
- PATENT PENDING

The **PD10-UL-M-KIT** is a field installable motorized latch pullback kit for Dor-o-matic/Falcon 1690/1790, First Choice 3600/3700, AHT4/5 & PD11 series devices. Retrofit mechanical devices in the field to electrified latch pullback devices while maintaining the UL Listing. This easy-to-install, robust kit from Command Access comes equipped with "Push to Set" technology making post installations adjustments a breeze! Check out the installation video below.

## SPECIFICATIONS

### VOLTAGE:

- Voltage range – 22 to 28VDC
- System protection – unit shutdown when voltage exceeds 28VDC
- Average Current Peak – 1A (High torque mode 2A)
- Average Current Hold -180mA (HT mode 250mA)
- PTS adjustment – approx. 1/4"

### WIRE RUN:

- 500' with 18ga wire
- 700' with 16ga wire

### PRODUCT DETAILS:

- Box: 10.5" x 3.75": x 2.5"
- Weight: 2 Lbs
- 15 Master Pack: 12.75" x 11.75" x 11"
- Weight: 30 Lbs

### RECOMMENDED UL LOCKING HARDWARE POWER SUPPLIES:

- PS204/PS204B
- PS210
- PS220/220B
- PS440B
- PS480B
- PS1
- PS2
- PS5-8

### FEATURES:

- MM4 Smart Module: On board diagnostics with audible feedback for adjustment and power issues
- "PTS": 5 second electronic adjustment for easy post installation adjustment
- Electric dogging rated for continuous duty - Auto retraction if dogged push pad is pulled from position
- Low current draw: Compatible with most 24VDC, 1A (or greater) regulated power supplies
- Field switchable to a "High Torque" mode
- Up to 500' wire run with 2-18 ga wire - Long wire runs provides installer with convenience of placing the locking device power supply in a centralized location; i.e. the same closet as the access panel
- 6' cable with Quick Connect for MM4 module to easily connect to power supply lead
- 3-year "no hassle" warranty

### ACCESSORIES:

- Request to Exit (REX) - Available as a field installable kit

## HOW TO ORDER

Part #	Easy Order #	Description
P10-UL-M-KIT	79240	Field Installable kit for 36" or 48" device. EU 24 VDC.
PD10REXKIT-ED	70870	Field installable REX kit. Single Pole Double Throw

**U.S. Customer Support**

**1-888-622-2377**

**Visit our website for more details**

**www.CommandAccess.com**

**Canada Customer Support**

**1-855-823-3002**