



- *700' wire runs (18/2 wire)*
- *24 VDC*
- *Low Current Draw*
- *3-Year Warranty*
- *Maintains Mechanical Dogging*

The easier and more affordable solution

Command Access electrified latch pullback modifications of the Adams Rite 8400 Mortise and 8600 CVR series storefront exit device are a high quality, cost effective solutions for new and retrofit applications. Our unique designs allow for centrally located power supplies and the cooling features of our patented PM300 modules ensure trouble free operation during "continuously on" conditions. These devices may be purchased as modification only. As a retrofit, the ARLP8400 & ARLP8600 models are designed to utilize the existing mounting locations and mortise or rod & case assemblies without having to remove the door. With efficient electronics and cost effective designs, the Command Access ARLP8400/ARLP8600 devices are advantageous solutions.

U.S. Customer Support
1-888-622-2377

Visit our website for more details
www.CommandAccess.com

Canada Customer Support
1-855-823-3002

Models Available

MDARLP8400EU24 - (fail secure)

Door is secure without power. Door is unlatched electronically. Latchbolt retracted by pushpad inside or electronically by adding power. Optional key cylinders and/or exit trim are available to retract the latchbolt from the outside

MDARLP8600EU24 - (fail secure)

Door is secure without power. Door is unlatched electronically. Latchbolt retracted by pushpad inside or electronically by adding power. Optional key cylinders and/or exit trim are available to retract the latchbolt from the outside

FEATURES:

- High-Performance quality solenoids designed for demanding applications
- Includes the patented PM300 interface power modules programmed to maximize the efficiency and life of the solenoid.
- Extended duration latch pullback capability for “continuously on” conditions
- The “local boost” design allows for centralized power supplies and extended wire runs up to 700’ with 18/2 wire
- Six foot power cable with quick connect for PM300 module
- The slim, compact design enables mounting on narrow-style doors
- Attractive low profile design projects less than 3” from the face of the door
- Retrofits Adams Rite 8400/8600 series
- Maintains factory dogging
- 3-year “no hassle” warranty

OPTIONS:

- REX - Request to Exit switch available factory installed or as a field installable kit
- LBM - Latch Bolt Monitor switch available on 8600 series only (factory installed only)
- Power Supply - PS1 for single door or two door simultaneous operation, PS2/PS2BB for up to two independently operated doors, PS5-8 for up to eight independently operated doors

SPECIFICATIONS:

- Non-handed
- Voltage - 24VDC
- Solenoid Amperage - Surge 6A for 200 ms / Holding - 250 mA @ 24V

MAXIMUM WIRE RUNS:

- 700’ with 18ga wire
- 1000’ with 16ga wire

Model No.	Notes:		
Customer:	Job No./Name:	Date:	Provided by: