

VLP-UL-M-KIT

- FAST, QUIET & SMOOTH OPERATION
- EASY TO INSTALL - NO MORE DRILLING!
- PTS "PUSH TO SET" TECHNOLOGY
- FULL PUSH PAD RETRACTION
- REQUEST TO EXIT INCLUDED!
- WORKS ON 33/35 & 98/99 SERIES



The newly redesigned **VLP-UL-M-KIT** is a practical and cost-effective way to convert a mechanical Von Duprin 33/35 or 98/99 series device to an electrified latch pullback device. The retrofit kit will maintain all UL listings on the device and is backed by CAT's 3-year no hassle warranty. The redesigned unit gets rid of all drilling or cutting from the previous model. It easily hooks onto the back activating bracket and is secured with (2) screws, in a matter of seconds. The only hole you'll need to drill is for the wire raceway. **PTS** allows for an easy post-installation adjustment of the latch/latches. A built-in REX switch is now standard on all units! Last but not least, all new VLP-UL-M-KIT's features an updated **MM4S** module with 3 different energy consumption settings from energy conscious to high torque to get the tough jobs done!

SPECIFICATIONS

VOLTAGE:

- Voltage range - 24 to 28 VDC
- System protection - unit shutdown when voltage exceeds 28VDC
- **Standard** - Average Current Peak: 900MA, Average Current Hold: 215mA
- **Low Current** - Average Current Peak: 600MA, Average Current Hold: 150mA
- **High Torque** - Average Current Peak: 2A, Average Current Hold: 250mA
- PTS adjustment - approx. 1/4"

WIRE RUN:

- 300' with 18ga wire

PRODUCT DETAILS:

- Box: 10.5" x 3.75" x 2.5"
- Weight: 2 Lbs
- 15 Master Pack:
- Weight: 30 ILbs 12.75" x 11.75" x 11"

CUTDOWN DETAILS:

- New 36" Model - Max Cut 7"
- New 48" Model - Max Cut 11"

FEATURES:

- Next Generation MM4S Smart Module: On board diagnostics with audible feedback for adjustment and power issues
- "PTS": 5 second electronic adjustment for easy post installation adjustment
- Electric dogging rated for continuous duty - Auto re-engage if push pad is pulled from dogged position
- Low Current Draw - Field switchable to a "Low Current" or "High Torque" mode
- Up to 300' wire run with 2-18ga wire - Long wire runs provides installer with convenience of placing the Command locking hardware power supply in a centralized location; i.e. the same closet as the access control panel
- 8' cable with Quick Connect for MM4S module to easily connect to power supply lead
- Request to Exit (REX) built-in at no charge
- 3-year "no hassle" warranty

U.S. Customer Support
 1-888-622-2377

Visit our website for more details
www.CommandAccess.com

Canada Customer Support
 1-855-823-3002



HOW TO ORDER

Part #	Easy Order #	Description
VLP-UL-M-KIT	79335	Kit for the Von Duprin 33/35 & 98/99 series. EU 24 VDC.
VDLBMKIT-ED*	79235	Field Installable Latchbolt monitor kit.

*Low current switches available call for more information

VLP-UL-M-KIT MATRIX

The VLP-UL-M-KIT will work in new installations and as a replacement for installations with existing electrifications, matrix lists available installation options.

Von Duprin Kit	Mechanical unmodified	CAT Modified Solenoid	CAT Modified Motor	VD Solenoid (EL)	VD Motor (QEL)	SDC Motor (LR100-VDK)	ACSI Motor (1550K-MDV)
VLP-UL-M-KIT	33/35 98/99	✓	✓	✓	✓	✓	✓

NEED A LOCKING HARDWARE POWER SUPPLY?

RECOMMENDED LOCKING HARDWARE POWER SUPPLIES:

- PS204/PS204B
- PS210
- PS220/220B
- PS440B
- PS480B
- PS1
- PS2
- PS-4
- PS5-8

