

CRL OVERHEAD CONCEALED DOOR CLOSERS

For Pricing Visit crlaurence.com or Call Us Toll Free at the Phone Numbers Shown on the Back Cover

CRL Jackson Overhead Concealed Door Closer Accessories

- For Use With Aluminum Framed Doors
- Non-Handed



CRL Jackson Deep Mortise Type Offset Arm and Slide Channel Assembly

- 7/8" (22 mm) Depth Top Rail
- Deep Mortise Type

The Deep Mortise Type Offset Arm Assembly includes a slide-track, offset arm, and all mounting hardware. The slide-track requires a minimum top rail depth of 7/8" (22 mm) to be mortised into the door.



CAT. NO.	OVERALL LENGTH	ARM FINISH
20900LC628	14" (356 mm)	Aluminum
20900LC313	14" (356 mm)	Dark Bronze

Minimum order: 1 each. All Closer Arms can be combined for quantity pricing.

CRL Jackson Shallow Depth Mortise Type Offset Arm and Slide Channel Assembly

- Shallow Depth 5/8" (16 mm) Top Rail

The shallow depth Offset Arm Assembly includes a slide-track, offset arm, and all mounting hardware. The slide track requires a minimum top rail depth of 5/8" (16 mm) to be mortised into the the door.



CAT. NO.	OVERALL LENGTH	ARM FINISH
201134LC628	12-7/8" (327 mm)	Aluminum
201134LC313	12-7/8" (327 mm)	Dark Bronze

Minimum order: 1 each. All Closer Arms can be combined for quantity pricing.

CRL Jackson Shallow Depth Mortise Type Offset Arm and Slide Channel Assembly

- Shallow Depth 5/8" (16 mm) Top Rail
- Provides Enhanced Pre-Load

The shallow depth Offset Arm Assembly includes a slide-track, offset arm, and all mounting hardware. The arm provides for enhanced pre-load. The slide track requires a minimum top rail depth of 5/8" (16 mm) to be mortised into the door.



CAT. NO.	OVERALL LENGTH	ARM FINISH
201312LC628	12-7/8" (327 mm)	Aluminum
201312LC313	12-7/8" (327 mm)	Dark Bronze

Minimum order: 1 each. All Closer Arms can be combined for quantity pricing.

CRL Jackson Offset Arm Assembly Covers

- Handed – Not Reversible
- Available in Two Finishes



Left Hand



Right Hand

- Fit All Arm Assemblies Shown Above

These Offset Arm Assembly Covers provide protection to the arm assembly and enhance the aesthetics of the installation.

Dimensions: W = 2" (51 mm)
H = 7/8" (22 mm)
L = 42-1/4" (1073 mm)

CAT. NO.	HANDING	FINISH
20106628	Left Hand	Aluminum
20106313	Left hand	Dark Bronze
20117628	Right Hand	Aluminum
20117313	Right Hand	Dark Bronze

Minimum order: 1 each. All Arm Covers can be combined for quantity pricing.