



TECHNICAL SPECIFICATIONS

Power Supply	110v / 60Hz
External Connections	2 USB, 2 RS232 serial ports, 1 LAN
Cutter Speed	6000 RPM
Key Reading / Decoding	Electrical contact
Mobile Capability	Requires pure sine wave inverter (sold separately)
Dimensions	12" x 15" x 14" (machine), 8" x 6" x 3" (console)
Weight	45 lbs.
Warranty	2 years

ACCESSORIES	PART NUMBER
A Jaw [Red]	B3311
B Jaw [Grey]	B3312
C Jaw [Green]	B3313
D Jaw [Blue]	B3314
G Jaw Kit [Yellow]	OPZ09486B (includes 1.5mm cutter, tracer and magnetic tip stop)
H Jaw	OPZ09523B (includes H jaw Allen tool and calibration template)
AD03 Adaptor	B3379 (for certain Lexus, Toyota and Subaru keys)
AD02 Adaptor	B3352 (for Infiniti Q45 and President models)
AV08 Adaptor	AV08 (for Ducati, Aprilia and Guzzi)
Vacuum Attachment	B3318

SPARE PARTS	PART NUMBER
2.5mm Cutter	B3320
Universal Tracer	RIC09483B
1.5mm Cutter (G Jaw)	RIC09617B
Magnetic Tip Stop	B3405
Cutter Install Tool	B3315



TECHNICAL SPECIFICATIONS

Power Supply	110v / 60Hz
External Connections	2 USB, 2 RS232 serial ports, 1 LAN
Cutter Speed	10,000 RPM (Laser side); 1500-3000 RPM (Edge Cut side)
Key Reading / Decoding	Electrical contact
Mobile Capability	Requires pure sine wave inverter (sold separately)
Dimensions	13" x 16" x 12" (machine), 8" x 6" x 3" (console)
Weight	80 lbs.
Warranty	2 years

ACCESSORIES	PART NUMBER
AC Jaw [included]	OPZ09734B
B Jaw [Grey]	OPZ09781B
D Jaw [Blue]	OPZ09783B
H Jaw	OPZ09523B (includes H jaw Allen tool and calibration template)
AD03 Adaptor	B3379 (for certain Lexus, Toyota and Subaru keys)
AD02 Adaptor	B3352 (for Infiniti Q45 and President models)
AV08 Adaptor	AV08 (for Ducati, Aprilia and Guzzi)
Console Arm Support	OPZ09454B

SPARE PARTS	PART NUMBER
2.5mm Cutter	B3320
Universal Tracer	RIC09483B
63mm Carbide Cutter	B5500
Magnetic Tip Stop	B3405
Standard Tip Stops	BA001