


Brass Rekeyable Padlocks

PL450 Premium Brass Rekeyable Padlocks

- Solid brass body and cylinder with chrome plated shackle provide superior corrosion resistance
- Keyable to most door lock cylinder keying systems using standard cylinder format (included cylinder drilled for 6-pins, pinned to 5)
- Hardened steel shackle and double-ball locking to resist cutting and prying
- Key-retaining and non-key-retaining offered, but easily convertible either way
- Shackle easily changed
- Boxed individually in shelf packs of 6 with 36 per master carton




Part#	CLK#	Width	Thickness	Shackle Diameter	Vertical Clearance	Horizontal Clearance
PL450B10S RK KW OBIT KR	cs480996	1-3/4"	13/16"	5/16"	1"	5/16"
PL450B10S RK KW OBIT NKR	cs480997	1-3/4"	13/16"	5/16"	1"	5/16"
PL450B10S RK LESS CYL W/DRVR	cs480998	1-3/4"	13/16"	5/16"	1"	5/16"
PL450B10S RK SC OBIT KR	cs480999	1-3/4"	13/16"	5/16"	1"	5/16"
PL450B10S RK SC OBIT NKR	cs481000	1-3/4"	13/16"	5/16"	1"	5/16"
PL450B10S RK SX OBIT KR	cs481001	1-3/4"	13/16"	5/16"	1"	5/16"
PL450B10S RK SX OBIT NKR	cs481002	1-3/4"	13/16"	5/16"	1"	5/16"



PL450B10S

PL400/300/200 Standard Brass Padlocks

- Solid brass body and parts along with chrome plated shackle prevent corrosion
- Hardened steel shackle resists cutting
- Non-key-retaining
- K120/1092VB (PL200) and K130/1092DS (PL300 & PL400) keyways
- Attractive blister pack supports retail sales
- Individually packed in shelf packs of 6 with 72 per master carton
- Original key blanks available. See page 32.



Part#	CLK#	Width	Thickness	Shackle Diameter	Vertical Clearance	Horizontal Clearance
PL200B10S KA 1A31 BP	cs503848	3/4"	3/8"	1/8"	7/16"	3/8"
PL200B10S KA GB2A BP	cs503849	3/4"	3/8"	1/8"	7/16"	3/8"
PL200B10S KD BP	cs503850	3/4"	3/8"	1/8"	7/16"	3/8"
PL300B10S KA 1B005 BP	cs510087	1-3/16"	1/2"	3/16"	5/8"	5/8"
PL300B10S KA GB3A BP	cs510090	1-3/16"	1/2"	3/16"	5/8"	5/8"
PL300B10S KD BP	cs503851	1-3/16"	1/2"	3/16"	5/8"	5/8"
PL400B10S KA 1G032 BP	cs503853	1-9/16"	9/16"	1/4"	7/8"	15/16"
PL400B10S KA GB4A BP	cs510091	1-9/16"	9/16"	1/4"	7/8"	15/16"
PL400B10S KD BP	cs503855	1-9/16"	9/16"	1/4"	7/8"	15/16"



PL200B10S

PL300B10S

PL400B10S