

Brass Resettable Padlocks

PL510 Brass Resettable Padlock

- Resettable Combination
- Brass Case with Brass Internal Parts Resists Corrosion
- Hardened Steel Shackle to Resist Cutting
- 10,000 Possible Combinations for Better Security
- Easy-Spin Dial for Quick and Simple Operation
- Attractive blister pack supports retail sales
- Individually packed in shelf packs of 6 with 48 per master carton

Example Order:
PL 510 P B 10 S BP

Padlock
 PL = Padlock

Series

Premium

Body Material
 B = Brass

Shackle Material
 S = Steel

Vertical Shackle Clearance
 10 = approx 1"
 20 = approx 2"

Packaging
 BP = Blister Pack

PL510B20S PL510B10S

Part#	CLK#	Width	Thickness	Shackle Diameter	Vertical Clearance	Horizontal Clearance
PL510PB10S BP	cs105930	2"	7/8"	5/16"	1-1/8"	1"
PL510PB20S BP	cs105931	2"	7/8"	5/16"	2-3/16"	1"

Interchangeable Core Padlocks

- Accepts all 6 or 7 pin SFIC-type cores
- Shackle easily changed
- Boxed individually in shelf packs of 6

PL452B/BC Premium Brass SFIC Padlocks

- Solid brass body with chrome plated shackle resists corrosion
- Brushed chrome plated version provides additional finish option and corrosion protection (BC model)
- Hardened steel shackle and double-ball locking to resist cutting and prying
- Key-retaining easily convertible to non-key-retaining

Example Order:
PL 452 S 10 S SFIC

Padlock
 PL = Padlock

Series

Body Material
 S = Steel
 B = Brass
 BC = Brushed Chrome Plated

Keyway
 SFIC = Prepared for small format interchangeable core

Shackle Material
 S = Steel

Vertical Shackle Clearance *
 10 = approx 1"
 20 = approx 2"

* For different clearance, purchase longer shackle separately. See page 32.

PL452BC10S SFIC PL452B10S SFIC

Part#	CLK#	Width	Thickness	Shackle Diameter	Vertical Clearance	Master Carton
PL452B10S SFIC	cs503842	1-3/4"	13/16"	5/16"	1"	<u>72</u>
PL452B20S SFIC	cs503844	1-3/4"	13/16"	5/16"	2"	<u>48</u>
PL452BC10S SFIC	cs503845	1-3/4"	13/16"	5/16"	1"	<u>72</u>
PL452BC20S SFIC	cs503846	1-3/4"	13/16"	5/16"	2"	<u>48</u>

PL452S Square Steel SFIC Padlocks

- Solid steel chrome plated body provides corrosion resistance
- Non-key-retaining
- Molybdenum shackle and double-ball locking to resist cutting and prying
- Master cartons of 36

Part#	CLK#	Width	Thickness	Shackle Diameter	Vertical Clearance
PL452S10S SFIC	cs510101	1-3/4"	3/4"	5/16"	1"
PL452S20S SFIC	cs510102	1-3/4"	3/4"	5/16"	2"

