



Chassis, Power Supplies & Accessories

Catalog 2014

Meridian Technologies, Inc.
700 Elmont Road, Elmont NY 11003
Tel: 516.285.1000 Fax: 516.285.6300
E-Mail: sales@meridian-tech.com
www.meridian-tech.com

Desk Chassis

1 Slot Desk Chassis

- SR-500/S 1 Slot Desk Chassis (24VAC or 12-28VDC version), WP-24 supply included
SR-500/SF 1 Slot Desk Chassis (24VAC or 12-28VDC version), w/flanges, WP-24 supply included

2 Slot Desk Chassis

- SR-1002/S 2 Slot Desk Chassis (24VAC or 12-28VDC), WP-24 supply included
SR-1002/SF 2 Slot Desk Chassis (24VAC or 12-28VDC), w/flanges, WP-24 supply included

3 Slot Desk Chassis

- SR-1350/S 3 Slot Wall mount Chassis, with 24VAC power supply
SR-1350T/S 3 slot Wall mount Chassis with micro fans & 24VAC power supply

4 Slot Desk Chassis

- SR-1450/S 4 Slot Wall mount Chassis, with 24VAC power supply

6 – Slot subrack 19" rack mount, 1RU high with Power supplies (110/220 VAC)

- SR-1600/S 19" Subrack, 1RU, 6 Slots with External power supply
SR-1600/R 19" Subrack, 1RU, 6 Slots with Dual External power supplies

Subrack Chassis

14 – Slot subrack 19" rack mount, 3RU high with 2 redundant Power supplies (110/220 VAC)

- SR-2001/AR1 19" Subrack stand-alone, 14 Slots, redundant Power Supplies
SR-2000/R1-PC 19" Master Subrack, 14 Slots, redundant Power Supplies, PC based diagnostics
SR-2001/ER1-PC 19" Subrack Expansion, 14 Slots, redundant Power Supplies, PC based diagnostics

18 – Slot Subrack

19" Rack Mount, 3RU High With 1 Power Supply (110/220 VAC)

SR-2001/AS1	19" Subrack Stand Alone, 18 Slots, with Power Supply
SR-2000/S1-PC	19" Master Subrack, 18 Slots, w/Power Supply, PC based diagnostic
SR-2001/ES1-PC	19" Subrack Expansion, 18 Slots, w/Power Supply, PC based diagnostics

SpectraSmart Chassis Interface cards

Comm-M	Communication Card for Master Chassis
Comm-S	Communication Card for Expansion Chassis
SS-INT	SpectraSmart chassis Interface Card

Cooling Fans , Power Supplies And Accessories

FA-2000/1	19"L x 1 3/6"H Fan Assembly Subrack w/3 fans (110V)
FA-2000/2	19"L x 1 3/6"H Fan Assembly Subrack w/3 fans (220V)

Wall Plug Power Adapters

WP-12D	12 VDC wall plug adapter (100mA), 110VAC input
WP-12D2	12 VDC wall plug adapter (500mA), 110 VAC input
WP-24A	24 VAC wall plug adapter (500 mA), 110VAC input
WP-24	24 VDC wall plug adapter (1000 mA), 110V / 220V AC input
WP-5D-1	5 VDC power supply for MT/MR-1HD module (110VAC) input
WP-5	5 VDC power supply for MT/MR-1HD module (110/220VAC) input

Power Supplies for Subracks

PS-100	Power supply for SR-1000/S model
PS-150	Power supply for SR-2000 series, 110/220 VAC
CD-BPL-S	1-Slot Blank Chassis Cover Plate
CD-BPL-D	2-Slot Blank Chassis Cover Plate

Power Supplies for Media converters and Ethernet switches

PSH24DC24	24VDC @ 1 Amp (24 watts) power supply
PSH24DC40	24VDC @ 1.7 Amps (40 watts) power supply
PSH48DC240	48VDC @ 5 Amps (240 watts) power supply
PSH48DC480	48VDC @ 10 Amps, 480 watts) power supply

Note: In order to use the SpectraSmart diagnostic features, it is necessary to use one of the diagnostic chassis (SR-2000/S1-PC, SR-2001/ES1-PC or SR-2000/R1-PC) as well as the diagnostic option (-D) on the modules in these chassis.

Cables

DB9M-RCA-4M/1	4-ch DB9 (male) to RCA cable, 1 meter, color coded RCA male connectors
DB9M-RCA-4F/1	4-ch DB9 (male) to RCA cable, 1 meter, color coded RCA female connectors

Adapters