

Components

Grade 1 Cylindrical Parts & Components

(to be used with L100 and LX100 series)

Part#	Description / Dimensions / Finish	CLK#
1DL 605 234 S	Dead latch, 2-3/4" Square Corner / US3	cs342518
1DL 605 238 S	Dead latch, 2-3/8" Square Corner / US3	cs342517
1DL 613 234 S	Dead latch, 2-3/4" Square Corner / US10B	cs342520
1DL 613 238 S	Dead latch, 2-3/8" Square Corner / US10B	cs342519
1DL 626 234 S	Dead latch, 2-3/4" Square Corner / US26D	cs342522
1DL 626 238 S	Dead latch, 2-3/8" Square Corner / US26D	cs342521
1DL EXT LINK FOR 3-3/4"	3-3/4" Ext. link for 2-3/8" Backset	cs498905
1DL EXT LINK FOR 5"	5" Ext. link for 2-3/4" Backset	cs436459
1SL 605 234 S	Spring Latch, 2-3/4" Square Corner / US3	cs342524
1SL 605 238 S	Spring Latch, 2-3/8" Square Corner / US3	cs342523
1SL 613 234 S	Spring Latch, 2-3/4" Square Corner / US10B	cs342526
1SL 613 238 S	Spring Latch, 2-3/8" Square Corner / US10B	cs342525
1SL 626 234 S	Spring Latch, 2-3/4" Square Corner / US26D	cs342528
1SL 626 238 S	Spring Latch, 2-3/8" Square Corner / US26D	cs342527
AS 605 W/SCREWS	ANSI Strike, US3 Bright Brass, Square Corner 1 Inch Wide	cs113694
AS 630 W/SCREWS	ANSI Strike, US32D Satin Stainless Steel, Square Corner 1 Inch Wide	cs113697
L1 IC-TP	For Grade 1 IC Lever	cs104397
L1 INSERT	Black Insert for Grade 1 Lever	cs101551
L1 RS	Lever Return Spring for L100	cs105041
L1 SP 605	Grade 1 Lever 605 Screwpack / US3	cs498918
L1 SP 613	Grade 1 Lever 613 Screwpack / US10B	cs498917
L1 SP 626	Grade 1 Lever 626 Screwpack / US26D	cs498916
L1 TP	For Grade 1 C Lever	cs103100
L195 TP	For L170 and L195 Lever	cs103102
L112 TB	Thru-Bolts for Grade 1 and Grade 2 Lever	cs502181
LK12 CYL CAP	Cylinder Cap for Grade 1 and Grade 2	cs106654
TS 605	T-Strike, Square Corner, US3	cs342529
TS 613	T-Strike, Square Corner, US10B	cs342530
TS 626	T-Strike, Square Corner, US26D	cs342531

Finishes:



626
U.S. = US26D
Satin Chrome



613
U.S. = US10B
Dark Bronze, Oil Rubbed



605
U.S. = US3
Bright Brass



L1 IC-TP



L1 TP



LK12 CYL CAP



TS 626

