

Multi-Technology Mobile Readers

Multiple Form Factors



OVERVIEW

Interlogix multi-technology mobile readers* work with the TruPortal™ access control system to provide instant mobile credential capabilities to the system. The 3MIL-R11030, 3MIL-R11320 and 3MIL-R11325 readers offer a compact design and basic multi-vendor compatibility.

Versatile Security System Compatibility

These multi-technology Wiegand-output readers work with all access control systems that use Wiegand-based data communications between 26 and 176 bits.

Optimizing any Environment

As smartphones and tablets become central to everyday life, Interlogix is leveraging mobile technologies to provide access control. The mobile readers deliver a smart alternative to plastic badges, offering greater convenience without compromising

security. Since people are rarely without their phones, this solution gives them another access option in addition to their keycards. The reader's design accommodates both metal and non-metal environments, and comes in a variety of wall and doorframe models for consistent read-range performance for various types of installations and climates.

Versatile and Rugged




For flexible migration to mobile credentialing, Interlogix mobile readers work with both TruPortal existing badges and mobile devices, and include a wide range of options that support Bluetooth 4.0 Low Energy. All Interlogix mobile readers feature a sleek, compact design.

A special version of the mobile reader can be hidden in a wall or ceiling or installed next to an existing reader without replacing it. This add-on reader provides Bluetooth® capability to most existing installations, allowing you to protect your investment in current readers and badges.

Multi-Technology Mobile Readers

Multiple Form Factors

Specifications

PART NO.		3MIL-R11030	3MIL-R11320	3MIL-R11325
				
Description		Interlogix® mini-mullion, in-line mobile reader, mobile smartphone credential support, as a stand-alone reader or to an existing reader	Interlogix US single-gang, multi-tech, mobile reader	Interlogix US single-gang with keypad, multi-tech, mobile reader
Mechanical	Dimensions	3.8 x 2.1 x 0.8 in. (96 x 52 x 21mm)	4.2 x 3.0 x 0.8 in. (120 x 76 x 21mm)	
	Housing	Molded polycarbonate/ABS		
	Finish	Black, textured, fingerprint resistant		
	Mounting	Anywhere within 10 ft. (3m) of legacy reader	Wall surface or standard US, UK or EU switchbox	
Environmental	Operating Temperature	-31°F - 149°F (-35°C - 65°C)		
	Humidity	0-100% RHNC		
	Ingress Protection Rating	IP65		
Electrical	Voltage	+5 VDC to +16 VDC		
	Normal Standby Current draw at 12 VDC	25mA	60mA	65mA
	Operating Current draw at 12 VDC	40mA	75mA	100mA
	Data Voltage	Rest >4 VDC / Active <1 VDC		
	Reader Interface	OSDP**, Weigand, Clock & Data Weigand, Clock & Data		
	Indication	1 RGB LED	1 RGB LED + illuminated keypad	
	Sounder	Integral speaker		
	Read Range	Up to 4 in. (10cm) for RFID cards, up to 30 ft. (9m) for Bluetooth®		
Reg.	Certifications	FCC Part 15, UL294, CE Marked, RoHS, WEEE		

**TruPortal does not support OSDP technology

Ordering Information

3MIL-R11030*	Interlogix In-line Add-on Reader. Mini-mullion form-factors add mobile smartphone credential support, as a stand-alone reader or to an existing reader. Black
3MIL-R11320*	Interlogix Mobile, US Single Gang, Multi-tech, Bluetooth, Black
3MIL-R11325*	Interlogix Mobile, US Single Gang with Keypad, Multi-tech, Bluetooth, Black

*Interlogix mobile readers available in the U.S. only.
**TruPortal supports Wiegand only input.

Compatible TruPortal Line Credentials

Model Number	Description
TP-PRX-CLAM-50PK	TruPortal Credential - HID® Proxcard® II Clamshell Design Cards - 50 pack
TP-PRX-KF-50PK	TruPortal Credential - HID® Prox Keyfobs - 50 pack
TP-PRX-ISO-50PK	TruPortal Credential - HID® Prox ISO Cards - 50 pack
TP-MFC-ISO-50PK	TruPortal Credential - MIFARE® Classic ISO Cards No Magstripe Gloss/Gloss - 50 pack
TP-MFC-ISOM-50PK	TruPortal Credential - MIFARE® Classic ISO Cards 2750oe Magstripe - Gloss/Gloss - 50 pack
TP-MFC-KF-BK-25PK	TruPortal Credential - MIFARE® Classic Keyfobs Piano Black - 25 pack
TP-MFC-KF-OG-25PK	TruPortal Credential - MIFARE® Classic Keyfobs Piano TruPortal Orange - 25 pack
TP-MFC-KF-LG-25PK	TruPortal Credential - MIFARE® Classic Keyfobs Epoxy Slender - TruPortal - 25 pack
TP-CP-KF-BK-25PK	TruPortal Credential - Interlogix Prox Keyfobs Piano Black - 25 pack
TP-CP-KF-OG-25PK	TruPortal Credential - Interlogix Prox Keyfobs Piano TruPortal Orange - 25 pack
TP-CP-KF-LG-25PK	TruPortal Credential - Interlogix Prox Keyfobs Epoxy Slender - 25 pack



interlogix.com

Specifications subject to change without notice.

© 2017 United Technologies Corporation.
All rights reserved.

All trademarks are the property of their respective owners. Interlogix is part of UTC Climate, Controls & Security, a unit of United Technologies Corporation.

2017/09 (GSP-2478)