

HID

Proximity and multiCLASS Readers

HID readers are compatible with HID 26-bit Wiegand and HID Kantech Secure Format (KSF) credentials. The readers are available in different shapes, sizes and read ranges. Kantech also offers multiCLASS card readers that are designed for customers upgrading their current card system from 125 kHz proximity technologies to iCLASS 13.56 MHz contactless smart card credentials. The customer has the ability to transition to smart cards over time while incorporating the use of multiple card technologies within a single building or across multiple facilities.

Features:

- Compatible with Kantech Secure Format (KSF) and HID proximity cards
- Two-factor verification (card plus PIN) reader models available
- Weatherproof, secure enclosure suitable for indoor or outdoor use
- Multicolor LED and beeper
- Migrate to iCLASS credentials using HID multiCLASS readers



"Access intelligence with HID readers"

Common Reader Specifications:	
Multicolor LED	
Integrated Beeper	

Operating Temperature Range: -30° to 65° C (-22° to 150°F) Maximum Cable Distance to Host: 150 m (500 ft)

integrated beoper	11100	,00,	
Model Number/Description	Dimensions (h x w x d)	Read Range/Linear Power Supply	Compatible Card Formats
HID-PP6005B	8.0 x 4.4 x 1.7 cm	Up to 7.5 cm (3 in)	Proximity KSF/HID
Mini Mullion Mount (Gray)	(3.1 x 1.7 x 0.7 in)	5-16 VDC	
HID-MP5365	15.2 x 4.3 x 2.54 cm	Up to 14 cm (5.5 in)	Proximity KSF/HID
Mullion Mount (Gray)	(6.0 x 1.7 x 1.0 in)	5-16 VDC	
HID-PR5355	12.7 x 12.7 x 2.54 cm	Up to 20 cm (8 in)	Proximity KSF/HID
Wall Mount (Gray)	(5.0 x 5.0 x 1.0 in)	10-28.5 VDC	
HID-PR5355KP	12.7 x 12.7 x 2.54 cm	Up to 20 cm (8 in)	Proximity KSF/HID
Wall Mount with Keypad (Gray)	(5.0 x 5.0 x 1.0 in)	10-28.5 VDC	
*HID-TL5395BE/BL/WH	11.9 x 7.6 x 1.7 cm	Up to 14 cm (5.5 in)	Proximity KSF/HID
Single Gang Box Mount	(4.7 x 3.0 x 0.7 in)	5-16 VDC	
HID-MX5375	30.5 x 30.5 x 2.54 cm	Up to 61 cm (24 in)	Proximity KSF/HID
Long Range Reader (Gray)	(12.0 x 12.0 x 1.0 in)	12/24 VDC	
HID-RP40-SE	12.2 x 8.4 x 2.4 cm	Up to 11 cm (4.25 in)	Proximity KSF/HID
Single Gang Box Mount (Black)	(4.8 x 3.3 x .95 in)	5-16 VDC	and Smart Cards
HID-RPK40-SE	12.2 x 8.4 x 2.7 cm	Up to 10 cm (4 in)	Proximity KSF/HID
Single Gang Mount with Keypad (Black)	(4.8 x 3.3 x 1.1 in)	5-16 VDC	and Smart Cards

* Model numbers vary by color. HID-TL5395BE (Beige), HID-TL5395BL (Black), HID-TL5395WH (White)

Related Products











HID

Proximity Cards and Fobs

HID proximity cards and fobs are available in a wide variety of styles suitable for every application. They are compatible with all HID readers and available with either HID 26-bit Wiegand or Kantech Secure Format (KSF).



Features:

- Available with either HID 26-bit Wiegand or Kantech Secure Format (KSF)
- KSF offers 16.7 million unique code combinations
- Dye sublimation (photo ID) printable cards
- Keyfob easily attaches to a key ring, badge clip or lanyard



"Inherent security and flexible design"

Model Number	Description	on Dimensions (h x w x t)		Slot Punch			
Kantech Secure Format (KSF) Card Format							
HID-C1326KSF	Clamshell Card	8.6 x 5.4 x 0.19 cm (3.4 x 2.1 x 0.075 in)	With PVC overlay	Vertical			
* HID-C1336KSF	ISO-Thin Card with Magnetic Stripe	8.6 x 5.4 x 0.076 cm (3.4 x 2.1 x 0.030 in)	Front Side	Vertical or Horizontal			
HID-C1346KSF	Keyfob	3.95 x 3.2 x 0.60 cm (1.55 x 1.25 x 0.235 in)	No	Key Ring Hole			
HID-C1386KSF	ISO-Thin Card	8.6 x 5.4 x 0.076 cm (3.4 x 2.1 x 0.030 in)	Front Side	Vertical or Horizontal			
HID-C1386K/G	ISO-Thin Card	8.6 x 5.4 x 0.076 cm (3.4 x 2.1 x 0.030 in)	Both Sides	Vertical or Horizontal			
26-bit Wiegand Card Format							
HID-C1326	Clamshell Card	8.6 x 5.4 x 0.19 cm (3.4 x 2.1 x 0.075 in)	With PVC overlay	Vertical			
* HID-C1336/GG	ISO-Thin Card with Magnetic Stripe	8.6 x 5.4 x 0.076 cm (3.4 x 2.1 x 0.030 in)	Both Sides	Vertical or Horizontal			
HID-C1346	Keyfob	3.95 x 3.2 x 0.60 cm (1.55 x 1.25 x 0.235 in)	No	Key Ring Hole			
HID-C1351	(Vehicle) Active Tag	9.3 x 6.8 x 0.76 cm (3.6 x 2.7 x 0.30 in)	No	No			
HID-C1386	ISO-Thin Card	8.6 x 5.4 x 0.076 cm (3.4 x 2.1 x 0.030 in)	Front Side	Vertical or Horizontal			
HID-C1386/GG	ISO-Thin Card	8.6 x 5.4 x 0.076 cm (3.4 x 2.1 x 0.030 in)	Both Sides	Vertical or Horizontal			

^{*} Magnetic stripe is not encoded

Related Products







