

1074 Series

ADA Barn & Pocket Door



1074-1 SHOWN



1074-2 SHOWN

The Trimco **1074 Series** Barn & Pocket Door Latchsets deliver a unique solution for sliding door applications. With 10 modern lever styles available, the 1074 Series is an ideal solution for offices and multi-family projects where high design is important. These latchsets are offered with either tubular or mortise locks for medium to high use situations. The 1074 Series is ADA compliant for use in public facilities.

APPLICATIONS

- Offices
- Hospitality
- Multi-Family & Mixed Use
- Commercial & Industrial Buildings

SLIDING DOOR LOCKS & PULLS

PRODUCT FEATURES

- Unique barn and slide door locking solution
- Americans with Disabilities Act (ADA) compliant
- Multiple functions for different applications
- 10 different lever styles to choose from
- Only requires 10 degrees of rotation to unlatch
- Privacy functions have button on inside and emergency access on outside

SPECIFICATIONS

STANDARDS



ANSI A117.1
Accessibility Code
(ADA Compliant)

WARRANTY

Lifetime Warranty

NOTES

2-3/8" backset on Tubular locks
2-3/4" backset on Mortise locks

MATERIAL OPTIONS

SS – Stainless Steel

FUNCTIONS

1074-1	Tubular Privacy
1074-2	Mortise Sectional Trim Privacy with Cylinder and Thumbturn
1074-2x5004	Mortise Sectional Trim with Occupancy Indicator
1074-2C	Mortise Sectional Trim with Constant Latching
1074-2E	Mortise Escutcheon Trim Privacy with Cylinder and Thumbturn
1074-2Ex5004	Mortise Escutcheon Trim with Occupancy Indicator
1074-3	Tubular Passage

FINISHES

629	Polished Stainless Steel
630	Satin Stainless Steel
SPEC	Special Options Available

1074 Series

ADA Barn & Pocket Door

HOW TO SPECIFY & ORDER



1074-1 SHOWN



1074-2 SHOWN

CHOOSE THE FOLLOWING

SERIES	HANDING	LEVER STYLE	FINISH
• 1074-1 Tubular Privacy • 1074-2 Mortise Sectional Trim Privacy with Cylinder and Thumbturn • 1074-2x5004 Mortise Sectional Trim with Occupancy Indicator • 1074-2C Mortise Sectional Trim with Constant Latching • 1074-2E Mortise Escutcheon Trim Privacy with Cylinder and Thumbturn • 1074-2Ex5004 Mortise Escutcheon Trim with Occupancy Indicator • 1074-3 Tubular Passage	• RH – Right Hand • LH – Left Hand	• SC001 - Bellini • ST001 - Munich • ST028 - Vienna • SC037 - Glen Ellen (More Styles Available)	• 630 Satin Stainless Steel • SPEC – Special Finish (See finish list for all options)

EXAMPLE

For an ADA privacy mortise sliding door latchset with Munich levers in satin stainless steel finish on a right hand door, specify or order: **1074-2.RH.ST001.630**

AVAILABLE LEVER STYLES



BELLINI



FRANKFURT



GLEN ELLEN



KOLN



MAHLER



MERRYVALE



MATISSE



MUNICH



STOCKHOLM



VIENNA

* Dimensions are informational only. Templates are available at www.trimcobbw.com