

AEGIS 7000V SERIES

VOIP MULTI TENANT TELEPHONE ENTRY SYSTEM



- 250 Tenants and 250 Access Codes
- No Phone Bill with Google Voice, Unlimited calls in United States and Canada Only.
- * *Google Voice and the Google logo are registered trademarks of Google Inc.*
- * *Must have Internet Connection*
- * *Must sign-up for free Google Voice Account*
- Use your existing VOIP Provider.
- Local programming via keypad with audio prompts
- **7000V MODEL:** 1x16 LCD 122mm x 33mm x 14mm (**VIEWING 13mm x9mm**)
- **7000VFF MODEL:** 1 x116 LCD 80mm x 36mm x13 mm (**VIEWING 6.5mm x 3mm**)
- Backlit Keypad Button
- Non-Volatile memory
- Single Relay
- Support pause dialing from the PBX
- Indoor or outdoor, surface and full-flush mount.
- Brushed Stainless Steel Faceplate *Warranty: 24 months*

SPECIFICATIONS

POWER INPUT: 12VAC/40VA (supplied) or 12-VDC/40VA with battery backup charging circuit.

CURRENT CONSUMPTION: 500mA idle, 700mA operating.

OPERATING ENVIRONMENT: 32°F to 140°F. *Heater is required if the temperature is below 32°F.*

NIGHT LIGHT: Super Bright Light Emitting Diode (LED).

CONSTRUCTION: 16 Gauge Cold Rolled Steel back box with enamel finished and Brushed Stainless Steel Faceplate

MOUNTING: Surface and full-flush.

DIMENSIONS:

Surface 10-13/16" (H) x 8-5/8" (W) x 3-3/4" (D).

Full-flush 10-13/16" (H) x 8-3/8" (W) x 2-7/16" (D)

MOUNTING RING FULL-FLUSH (FFM7 is included on 7150FFP and 7250FFP):

Inside 11-1/8" (H) x 8-11/16" (W) x 2-5/8" (D)

Outside 14-5/16" (H) x 12-1/8" (W)

SHIPPING WEIGHT: 10-12 lbs approximate.

ORDERING PART

Surface Mount

7000V

250 tenants 250 access codes

Full-flush Mount

7000VFF

250 tenants 250 access codes

ACCESSORIES

Video Package

UVPC Color Camera Package

UVPB Video Balun for Twisted Pair video transmission

Pedestal Mounting Post, Adapter Plate and Mounting Ring

UPM1S Standard Single Arm (42"H, 5"x5" base)

UPM4S Standard Single Arm (47"H, 5"x5" base)

UPM1L Large Single Arm (47"H, 8"x8" base)

UPM6L Large Single Arm (64"H, 8"x8" base)

UPM2 Double Vertical Arm (44"/84"H, 8"x8" base)

UPM5 Double Horizontal Arm (47"H, 8"x8" base)

UPMDB64 Single Arm Direct Buriel (64"H)

UAP78 Adapter Plate AeGIS 8000P Series

UPM12E 12" Expansion Arm use for all UPM

Miscellaneous Accessories

USP1 AC and Telephone Surge Protector.

USP2L Surge and Lightning Protection, *include Lightning on 24 months warranty*

AHP5 Heater Pad with Thermostat.

UBAT1 12VDC 4.5 Amp Hour backup battery.

UXIT Multipurpose push button switch

Specifications subject to change without prior notice

PACHCO
Since 1978

Home of Telephone Entry Access Control Systems

San Clemente, California
1-888-678-7224
www.pach-co.com