

PLP-UNM
PLP-UNL



Display size

PLP-UNM - 22" to 50"
PLP-UNL - 32" to 90"



Max load

150lb
(68.2kg)

Universal I-Shaped Adaptors

FOR 22" TO 90" DISPLAYS

The Universal I-Shaped Adaptors offer mounting compatibility for medium to large sized displays weighing up to 150lb (68.2kg). The new I-shaped design has been created to help prevent blocking the display's power and signal input locations, making installation quick and easy. For added compatibility, the I-Shaped Adaptors are designed to attach to many Peerless-AV® mounts using either a VESA® 100 x 100mm or PLP mounting pattern. Mount your display with confidence knowing the included security hardware will help prevent theft.

The Universal I-Shaped Adaptors provide easy connection to many Peerless-AV® flat panel mounts with a VESA® 100 x 100mm or PLP mounting pattern.




Additional Features

- ✓ Universal I-Shaped Adaptors fit virtually any display weighing up to 150lb (68.2kg) (actual mount capacity may be less)
- ✓ Compatible with many Peerless-AV® display mounts (mounts sold separately)
- ✓ ACC-M1020 required when mounting to Peerless-AV PLP mounting pattern (sold separately)
- ✓ Provided with display mounting security hardware for effective theft deterrence
- ✓ Heavy gauge cold rolled steel construction
- ✓ Designed to prevent blocking the display's power and signal inputs
- ✓ Works in landscape or portrait orientation


UNIVERSAL MOUNTING PATTERN

PLP-UNM is compatible with displays having VESA® mounting pattern from 200 x 200 to 400 x 400mm

PLP-UNL is compatible with displays having VESA® mounting pattern from 200 x 200 to 600 x 400mm



PLP-UNL



PLP-UNM



Shown with Peerless-AV Ceiling Mount, PLCM-1



Model Numbers

WARRANTY: Limited 5-year

PLP-UNM: Universal I-Shaped Adaptor for 22" to 50" Displays
PLP-UNL: Universal I-Shaped Adaptor for 32" to 90" Displays

Product Specifications


	DIMENSIONS (W x H x D)	PRODUCT WEIGHT	LOAD CAPACITY	FINISH	AVAILABLE COLORS
PLP-UNM	16.50" x 16.78" x 0.71" (419 x 425 x 18mm)	4.30lb (1.95kg)	150lb (68.2kg)	Powder Coat	Black
PLP-UNL	24.38" x 16.78" x 0.71" (619 x 425 x 18mm)	5.17lb (2.3kg)			

Package Specifications

	PACKAGE SIZE (W x H x D)	PACKAGE SHIP WEIGHT	PACKAGE UPC CODE	PACKAGE CONTENTS	UNITS IN PACKAGE
PLP-UNM	25.50" x 5.13" x 1.88" (647.7 x 130.30 x 47.75mm)	5.44lb (2.5kg)	PLP-UNM: 735029244851	I-Shaped Adaptor plate, mounting hardware, display mounting hardware and wrench	1
PLP-UNL		6.30lb (2.9kg)	PLP-UNL: 735029241331		

Compatible with: Many Peerless-AV® Display Mounts
 Contact Peerless-AV Customer Care for more information.

All dimensions = inch (mm)



Architect Specifications

The Universal I-Shaped Adaptor shall be a Peerless-AV model PLP-UNM or PLP-UNL and shall be located where indicated on the plans. Assembly and installation shall be done according to instructions provided by the manufacturer.

Visit peerless-av.com to see the complete line of AV solutions from Peerless-AV, including outdoor displays, wireless, kiosks, digital audio, display mounts, projector mounts, carts/stands, and a full assortment of accessories.

Peerless-AV
 2300 White Oak Circle
 Aurora, IL 60502 USA
(800) 865-2112
(630) 375-5100
Fax: (800) 359-6500

Peerless-AV Europe
 Unit 3 Watford Interchange
 Colonial Way, Watford
 Herts, WD24 4WP
 United Kingdom
+44 (0) 1923 200100
Fax: +44 (0) 1923 200101

Peerless-AV de México
 Ave de las Industrias 413
 Parque Industrial Escobedo
 Escobedo, N.L.,
 Mexico 66050
+52 (81) 8384-8300
Fax: +52 (81) 8384-8360

