

STI POLYCARBONATE ENCLOSURE



STI-7500A



STI-7511D

PRODUCT OVERVIEW

Multipurpose lockable enclosure for a wide range of larger size devices, components and instruments, such as keypads, annunciators and automated external defibrillators (AEDs) which require protection from vandalism, accidental damage, as well as the elements, such as dirt and grime. Spacers, integrated hinge and covers are formed from tough polycarbonate material. The polycarbonate enclosures are backed by a three year guarantee against breakage and damage in normal use. STI enclosure is lockable with either a key or thumb lock.

KEY FEATURES

General Information

- Protection for large units against physical damage, grime and severe environments.
- Can be used over volume or lighting controls.
- Each protected unit can be clearly seen and quickly identified.
- Three year guarantee against breakage of polycarbonate in normal use.

Construction

- 94V-2 flammability rating.
- Cover, integrated hinge and spacers are formed from tough polycarbonate material.

Installation

- Fast and easy installation.
- Mounting hardware and gaskets are included.
- Typical working properties of polycarbonate are -40° to 250°F (-40° to 121°C).

Options



- Key or thumb lock available.

STI Polycarbonate Enclosure

Dimensions and Technical Information

BUILD YOUR MODEL

STI-75



ENCLOSED BACK BOX

A = Enclosed deep back box
B = Enclosed back box with double-gang electrical box
F = Enclosed back box

OPEN BACK BOX


C = Open back box for flush mount applications
D = Open conduit back box, surface mount applications
E = Open back box for flush mount applications

*STI-7510 and STI-7511 with back box "A", "E" or "F" also available in white polycarbonate. Add "-OW" to the part number (i.e. STI-7510A-OW).

Accessories

KIT-H18021 NEMA 4X 3/4" rigid conduit hub for "A" back box
KIT-H18054 Two replacement keys #CH751
KIT-318 Adapter plate used for mounting "A", "B" or "F" back box to pedestal
KIT-6297B20 3/4" conduit hub for "B", "C" and "F" back boxes
STI-1283 Backplate

NOTE: Below pictures illustrate back box differences.



APPROVALS & WARRANTY


WARRANTY

Three year guarantee against breakage of polycarbonate in normal use.


NOTICE

STI recommends replacement of gaskets every five years for outdoor applications.

B A C K X	STI-7500/7501				
	G	H	K	L	
A	8.48	5.40	6.48	3.40	
B	8.50	5.40	5.50	0.55	
C	7.81	4.80	5.25	1.76	
D	7.73	5.40	5.70	2.79	
E	7.70	5.40	5.71	1.01	
F	8.30	4.80	5.63	1.60	



B A C K X	STI-7510/7511		
	M	N	P
A	8.48	6.48	4.59
B	8.50	5.50	1.74
C	7.81	5.25	2.95
D	7.73	5.70	3.98
E	7.70	5.71	2.20
F	8.30	5.63	2.79



Safety Technology International

2306 Airport Road
Waterford, Michigan
48327, USA

Tel: 248-673-9898
Fax: 248-673-1246
Toll-free: 800-888-4784
info@sti-usa.com
www.sti-usa.com

Taylor House
34 Sherwood Road
Bromsgrove, Worcestershire
B60 3DR, England

Tel: +44 (0)1527 520 999
Fax: +44 (0)1527 501 999
info@sti-emea.com
www.sti-emea.com