

User-friendly surveillance at a budget-friendly price

Now with:
Intuitive user interface
Mac® Safari® browser plug-in support



Quick & Easy Installation

- 1 Install cameras
- 2 Connect them to the NVR
- 3 Power up the NVR

- A complete "all-in-one" IP video solution
- Plug-and-Play camera auto-configuration
- Built-in PoE switch to power cameras
- HD performance at an analog system price

TruVision® NVR 10 & Megapixel Camera Kits



Works with
TruVision® Navigator

Ideal for small retail stores, medical offices, gas stations and residential applications, the TruVision® NVR 10 IP video kit from Interlogix provides a complete, cost-effective surveillance solution that's also incredibly easy to install.

Available in 4- and 8-channel configurations, each kit includes a choice of TruVision cameras with no IP configuration or programming required. Simply install the cameras, connect to the built-in PoE switch and power on the NVR to start recording. Manage multiple recorders with the free downloadable TruVision Navigator VMS software and view cameras on-the-go with the free TVRmobile app.

NVR Features

- Easy front panel direct channel selection
- Monitor/Mouse ports – No PC required
- Continuous, motion or scheduled recording modes
- Event recording
- One-push Archive button to USB drive
- Up to 8 built-in PoE ports
- 20 or 40Mbps bandwidth
- 1 or 2TB of storage

Camera Features

- 2MPx Bullet IR Cameras
- 2MPx Turret IR Cameras
- 2MPx or 4MPx Wedge IR Cameras
- H.264 compression
- WDR
- True day/night
- Indoor/Outdoor - IP66 rated
- PoE/12VDC
- Supports PSIA and ONVIF open standards

Video Software

- TruVision Navigator
- TVRmobile HD App
- TruVision Device Finder



4-Channel IP Video Kits



TVN-1004-KB4



TVN-1004-KW4



TVN-1004-KT1

Model	Description	NVR	Cameras
TVN-1004-KB4	4-Channel Kit w/4 2MPx IR Bullet (4mm lens) Cameras Kit	1 x TVN-1004cS-1TB : 4-Channel NVR 10 Compact w/ Built-in 4-Port PoE Switch, 1TB Storage	4 x TVB-5301 : 2MPx Open Standards IR Bullet (4mm lens) Cameras
TVN-1004-KW4	4-Channel Kit w/4 2MPx Wedge Cameras Kit	1 x TVN-1004cS-2TB : 4-Channel NVR 10 Compact w/ Built-in 4-Port PoE Switch, 2TB Storage	4 x TVW-5302 : 2MPx Open Standards Low-profile Mini Dome IR Wedge (2.8mm lens) Cameras
TVN-1004-KT1	4-Channel Kit w/4 2MPx Turret Cameras Kit	1 x TVN-1004cS-1TB : 4-Channel NVR 10 Compact w/ Built-in 4-Port PoE Switch, 1TB Storage	4 x TVT-5301 : 2MPx Open Standards IR Turret (2.8mm lens) Cameras

8-Channel IP Video Kits



TVN-1008-KB4



TVN-1008-KW4 / TVN-1008-KW6



TVN-1008-KT1



TVN-1008-KW5

Model	Description	NVR	Cameras
TVN-1008-KB4	8-Channel Kit w/4 2MPx IR Bullet (4mm lens) Cameras Kit	1 x TVN-1008S-2TB : 8-Channel NVR 10 w/Built-in 8-Port PoE Switch, 2TB Storage	4 x TVB-5301 : 2MPx Open Standards IR Bullet (4mm lens) Cameras
TVN-1008-KW4	8-Channel Kit w/4 2MPx Wedge Cameras Kit	1 x TVN-1008S-2TB : 8-Channel NVR 10 w/Built-in 8-Port PoE Switch, 2TB Storage	4 x TVW-5302 : 2MPx Open Standards Low-profile Mini Dome IR Wedge (2.8mm lens) Cameras
TVN-1008-KW6	8-Channel Kit w/4 4MPx Wedge Cameras Kit	1 x TVN-1008S-2TB : 8-Channel NVR 10 w/Built-in 8-Port PoE Switch, 2TB Storage	4 x TVW-5305 : 4MPx Open Standards Low-profile Mini Dome IR Wedge (2.8mm lens) Cameras
TVN-1008-KT1	8-Channel Kit w/4 2MPx Turret Cameras Kit	1 x TVN-1008S-2TB : 8-Channel NVR 10 w/Built-in 8-Port PoE Switch, 2TB Storage	4 x TVT-5301 : 2MPx Open Standards IR Turret (2.8mm lens) Cameras
TVN-1008-KW5	8-Channel Kit w/6 2MPx Wedge Cameras Kit	1 x TVN-1008S-2TB : 8-Channel NVR 10 w/Built-in 8-Port PoE Switch, 2TB Storage	6 x TVW-5302 : 2MPx Open Standards Low-profile Mini Dome IR Wedge (2.8mm lens) Cameras

TruVision® is proudly distributed by:



interlogix.com

Specifications subject to change without notice.

© 2017 United Technologies Corporation.
All rights reserved.

All trademarks are the property of their respective owners.
Interlogix is part of UTC Climate, Controls & Security,
a unit of United Technologies Corporation.

2017/10 (GSP-2623)