

# C5 SERIES CREDENZA RACKS



shown with optional SRSR Series pull-out rack and display mount

## DEEPER C5 SERIES CREDENZA RACKS

Improved for a Wider Range of Applications

- Extended depth accommodates deeper equipment, such as Middle Atlantic UPS models and AV matrix switchers. Allows greater flexibility for drop-in connection boxes
- Enhanced cooling includes 50 CFM energy-saving, thermostatically-controlled DC blowers in each bay. Quiet and powerful: 50 CFM 29 dB (see A&E spec #96-01180 for measured values)
- Additional options for conferencing include flat screen (42" – 70") and multi-position camera mounts

27-1/2" Deep Credenza Racks (Standard Depth)							31-1/2" Deep Credenza Racks					
Frame**		Finishing Kit, Traditional Style			Finishing Kit, Contemporary Style		Frame**		Finishing Kit, Traditional Style		Finishing Kit, Contemporary Style	
# of Bays	120V Model	220V Model	With Smoked Plexi Door(s)	With Solid Door(s)	With Smoked Plexi Door(s)	With Solid Door(s)	# of Bays	Model	With Smoked Plexi Door(s)	With Solid Door(s)	With Smoked Plexi Door(s)	With Solid Door(s)
1 Bay	C5F1	IC5F1	C5K1-TPD-xx *	C5K1-TSD-xx *	C5K1-CPD-xx *	C5K1-CSD-xx *	1 Bay	C5F1-D	C5K1-D-TPD-xx *	C5K1-D-TSD-xx *	C5K1-D-CPD-xx *	C5K1-D-CSD-xx *
2 Bay	C5F2	IC5F2	C5K2-TPD-xx *	C5K2-TSD-xx *	C5K2-CPD-xx *	C5K2-CSD-xx *	2 Bay	C5F2-D	C5K2-D-TPD-xx *	C5K2-D-TSD-xx *	C5K2-D-CPD-xx *	C5K2-D-CSD-xx *
3 Bay	C5F3	IC5F3	C5K3-TPD-xx *	C5K3-TSD-xx *	C5K3-CPD-xx *	C5K3-CSD-xx *	3 Bay	C5F3-D	C5K3-D-TPD-xx *	C5K3-D-TSD-xx *	C5K3-D-CPD-xx *	C5K3-D-CSD-xx *

Frame Model & Finishing Kits compatible w/ Monitor Mounts					
Frame (31-1/2" Deep**)		Finishing Kit, Traditional Style		Finishing Kit, Contemporary Style	
# of Bays	Model	With Smoked Plexi Door(s)	With Solid Door(s)	With Smoked Plexi Door(s)	With Solid Door(s)
2 Bay	C5F2	C5K2-TPD-xx*	C5K2-TSD-xx*	C5K2-CPD-xx*	C5K2-CSD-xx*
3 Bay	C5F3	C5K3-TPD-xx*	C5K3-TSD-xx*	C5K3-CPD-xx*	C5K3-CSD-xx*

**Note: A complete system includes the frame & the finishing kit – when ordering a finishing kit the frame must also be ordered. \*\*Frame does not come with finishing kit.**

\*Replace 'xx' with DS = Darkstone, GS = Graystone, PS = Pepperstone, SG = Shark Gray, EA = Ebony Ash, WG = Wenge, DC = Dark Cherry, DP = Dark Pecan, AG = Aged Cherry, HM = Honey Maple, LW = Light Walnut, MP = Maple.

### STANDARD WORK SURFACE FINISHES



# C5 SERIES CREDENZA RACKS

## SINGLE & DUAL MOUNTS FOR C5 SERIES CREDENZA RACKS

Now you can easily mount large format monitors directly to C5 Series credenzas. Eliminates wall mounting and cable routing issues with built-in cable pathways.

- Accommodates most screens from 42" to 65" (dual) or 70" (single). Larger sizes available custom - please call
- Monitor height is adjustable and easy to level using the provided markings
- Optional camera mounts are ideal for videoconferencing systems. Cameras can be mounted above or below single monitors, or between dual monitors. Mounts are fully adjustable – choose from a large or small platform to match your camera unit size
- Includes cable clips for neat cable management into the credenza racks below
- Durable black powder coat finish

## C5 SINGLE AND DUAL LARGE FORMAT MONITOR MOUNTS

Part #*	Description	*MONITOR MOUNTS SOLD SEPARATELY. Requires pre-Machined Top (finishing kit) designated in finishing kit part # (EG: C5K2-CPDMT-xx). Available for 2 & 3 bay C5 only.
C5MM1-4270S	fits 42" to 70" single monitor, accepts optional camera mounts	
C5MM1-4255D	fits 42" to 55" dual monitors, accepts optional camera mounts	
C5MM1-5665D	fits 56" to 65" dual monitors, accepts optional camera mounts	

## C5 UNIVERSAL CAMERA MOUNTS

Part #	Description	Shelf Size
C5CMTB-88	mounts to top or bottom of screens	8" x 8"
C5CMTB-128	mounts to top or bottom of screens	12" x 8"
C5CMM-88	mounts between dual screens	8" x 8"



3 bay credenza shown with **C5MM1-4255D** dual monitor mount



2 bay credenza shown with **C5MM1-4270S** single monitor mount

## C5 DEPTH EXTENDER

Install deeper equipment in C5 credenza racks with the C5 depth extender. The Depth Extender Kit is field-installable and extends the rear depth of any single bay of any standard depth C5 Credenza model to accommodate deeper components and their cables. The extender adds nearly 3" to the frame's useable depth (while staying within the overall depth of the wood surface) and accommodates the unit's standard rear panel. Fits all models and installs with an included wrench.

Part #	Shown in gray for clarity
C5-EXT*	



Extender kit adds 2.84" useable depth

## OPTIONS FOR 31-1/2" DEEP CREDENZA RACKS

		
<b>12 Space Rotating Sliding Rail System</b>	<b>Flip-Up Side Shelf Contemporary Style</b>	<b>Flip-Up Side Shelf Traditional Style</b>
C5D-SRSR12**	C5D-SDSH-Cxx*	C5D-SDSH-Txx*

\*\*Note: weight capacity is 125 lbs.

\*Replace 'xx' with DS = Darkstone, GS = Graystone, PS = Pepperstone, SG = Shark Gray, EA = Ebony Ash, WG = Wenge, DC = Dark Cherry, DP = Dark Pecan, AG = Aged Cherry, HM = Honey Maple, LW = Light Walnut, MP = Maple.

## MILLWORK KIT

A complete kit to facilitate the creation of custom millwork.

This kit includes all required drawings in electronic format, and all of the required mounting and assembly hardware (handles/pulls not included).

Part #	For Use With
C5-MK1	standard and deep 1 bay C5 frame
C5-MK2	standard and deep 2 bay C5 frame
C5-MK3	standard 3 bay C5 frame
C5-MK3-D	deep 3 bay C5 frame