

USB to Serial Adapter Cable (USB-A to DB9 M/M), 5-ft.

MODEL NUMBER: **U209-000-R**



Description

The U209-000-R USB-to-Serial Adapter Cable allows you to connect a 9-pin RS-232 serial device to a computer or laptop with a USB Type-A port. It works with modems, digital cameras, PDAs, ISDN terminals and other devices with a serial port. The U209-000-R supports data transfer speeds up to 230 Kbps—twice as fast as a built-in serial port. No external power is required, and the compact 5-foot cable tucks away conveniently in your backpack or laptop bag for easy travelling. Doubled-shielded design with gold-plated contacts, tinned copper braid and aluminum Mylar foil shield eliminates crosstalk and reduces EMI/RFI interference. Compatible with Windows 2000, XP, Server 2003, Vista, 7, Server 2008, 8, 8.1, Server 2012, and 10; Mac OS X 10.6 through 10.12; and Linux Redhat 7.3, 8.0 and 9.0. Also works with [Android tablets and smartphones](#) with the addition of a [USB Host Mode \(OTG\) cable](#).

Features

- Connect a RS-232 Serial device to the USB port on your computer or Android tablet / phone
- Compatible with Android tablets / phones with USB Host Mode (OTG) support and OS version 3.2 and above
- Connectors: USB-A male/DB9 male
- Portable design is ideal for use with a PDA or digital camera
- Does not require external power
- Supports data transfer rates up to 230 kbps
- Premium double-shielded cable with tinned copper braid and aluminum Mylar foil shield that eliminates cross-talk and reduces EMI/RFI interference
- Compatible with Windows, Mac and Linux computers, and Android Tablets / Phones (See System Requirements for details)
- Prolific PL2303RA Chipset

Specifications

INPUT

Highlights

- 5 ft. Length
- No external power required
- Compatible with Windows, Mac and Linux computers, and Android Tablets / Phones (See System Requirements for details)
- Need drivers? Click on the Support Page link on the left

System Requirements

- Compatible with Windows 2000, XP, Server 2003, Vista, 7, Server 2008, 8, 8.1, Server 2012, and 10
- Compatible with Mac OS X 10.6 through 10.12
- Compatible with Linux Redhat 7.3, 8.0 and 9.0 (Linux Kernel 2.4.31 and above already includes built-in drivers)
- Compatible with Android Devices (Tablets with USB Host Mode (OTG) support and Android OS version 3.2 and above. Android Devices will require a USB Host Mode (OTG) cable (such as Tripp Lite's U052-06N) to connect the U209-000-R to the device.

Package Includes

- U209-000-R USB-to-Serial Adapter Cable
- Owner's Manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (ft.)	4.9
Cable Length (m)	1.5
PHYSICAL	
Color	Black
CONNECTIONS	
Ports	1
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	DB9 (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>