



The pictures to the left are for illustration purposes only.

WV-ASM970 VERSION 10

IP MATRIX CLIENT SOFTWARE

- Multi-monitor option enables simultaneous use of operation screen and monitor screen (1 / 4 / 7 / 9 / 10 / 13 / 16 split) on a dedicated monitor; two-monitor operation is also available
- Up to 30 ips/camera can be displayed in 16 split screens in MPEG-4 2 Mbps mode (depending on the camera, camera setup and PC performance)
- Up to 30 ips/camera can be displayed in 16 split screens in H.264 1.5 Mbps mode with VGA (depending on the camera, camera setup and PC performance)
- Image resolution dynamically changes depending on the screen mode: VGA for quad screen, QVGA for 16 split screens, enabling optimum network usage (depending on the camera mode)
- Decoder mode supported (WV-ASM970 can be used as PC-based decoder instead of GXD400)
- WV-ASE902: Max. 16 screen x 4 monitor support

SYSTEM COMPONENTS

IP Matrix Client Software

WV-ASM970



The picture above is for illustration purposes only.

Ethernet System Controller with 3D-Joystick and Jog/Shuttle

WV-CU950



WV-ASM200

I-PRO MANAGEMENT SOFTWARE

- Supports 16:9 video stream and 16:9 HD monitor; displays 16:9 and 4:3 videos from IP cameras on the same screen
- H.264 recording data in the SD/SDHC memory card can be downloaded
- Convert file format from n3r (proprietary format) to MP4 and WMV
- Up to 100 recorders, 64 encoders and 256 directly connected cameras can be registered
- Up to 6,400 cameras registered in the recorders and 256 cameras registered in the encoders are automatically registered in the WV-ASM200 (the number of cameras depends on the recorder and encoder)
- Up to 16x 30 ips/camera images can be displayed in H.264 1.5 Mbps mode
- Fisheye image correction/de-warp
- Software License Products
 - WV-SAE100W: Face Detection XML
 - WV-SAE200W: iVMD

WV-ASE201W / ASE202W / ASE203W / ASE204W / ASE205W / ASE231W

EXTENSION SOFTWARE

- WV-ASE201W: Three monitors, system controller (WV-CU950) support
- WV-ASE202W: Max. 64 screen support
- WV-ASE203W: Increases number of recorder registration
- WV-ASE204W: Supports WJ-GXD400
- WV-ASE205W: Image compensation (Fog/Snow)
- WV-ASE231W: Client for WV-ASF900

OPTIONAL ACCESSORY

Ethernet System Controller with 3D-Joystick and Jog/Shuttle

WV-CU950

(WV-ASE201W is necessary)



BB-HNP17A

NETWORK CAMERA RECORDER WITH VIEWER SOFTWARE

- H.264, MPEG-4 and JPEG recording
- Supports the recording and playback of H.264 i-PRO IP cameras
- Supports resolutions of 1280 x 960
- Remote access function
- Up to 64 cameras register
- Event detection recording
- Flexible layout
- Preset sequence
- Timer recording with preset designation
- Pop-up display
- Time-specified color night view