

ioProx

Receiver and Wireless Transmitter

The ioProx Transmitter is ideal for long-range (up to 45 m/150 ft) applications such as opening parking gates. The transmitter is available with an optional integrated ioProx tag, which can be read by an ioProx card reader, making it an ideal solution to access both a parking facility and an office building without searching for multiple access cards. The ioProx transmitter uses radio-frequency (RF) technology secured with encrypted coding. The ioProx Receiver is field selectable for either 26-bit Wiegand format or for Kantech Extended Secure Format (XSF).


Features:

- Four-channel receiver can be matched to a button on the transmitter
- Long read range - up to 45 m (150 ft)
- Encrypted code ensures high level of security
- Two or four-button transmitter with optional integrated ioProx tag
- Indoor/outdoor use





“Long-range secure transmission”

| Model Numbers: | |
|----------------|--|
| P700WLS | Four-channel receiver, standard whip antenna |
| P82WLS | Two-button transmitter |
| P82WLS-TAG | Two-button transmitter, integrated ioProx tag |
| P84WLS | Four-button transmitter |
| P84WLS-TAG | Four-button transmitter, integrated ioProx tag |
| Accessories: | |
| P-WLS-A1 | Standard whip antenna |
| P-WLS-A2 | Dipole antenna |



Related Products



Polaris

Magnetic Stripe Readers and Cards

Polaris magnetic stripe readers and cards combine quality, reliability and installation flexibility. Rugged and affordable, the readers mount on a wall or door mullion. A simple motion through the card slot (in either direction) reads a card. A bi-color LED flashes to confirm that a card has been read. The LED changes color when the door unlocks. Polaris integrates with an access control system using either 26-bit/34-bit/ABA) Wiegand or ABA-Clock-and-Data input. Integrated keypad model available for dual authentication.

Features:

- Weatherproof reader for indoors/outdoors
- Long life read head - 1,000,000 swipes
- Fast bi-directional card reading
- High coercivity magnetic stripe card
- Card lasts for over 25,000 swipes
- All cards are pre-programmed



“Cost-effective and easy-to-use”

| Model Numbers: | |
|----------------|---|
| POL-2 | Magnetic stripe reader |
| POL-25M | Magnetic stripe reader with 5 m (16 ft) cable |
| POL-2KP | Magnetic stripe reader with integrated keypad |
| POL-2KP-5M | Magnetic stripe reader with integrated keypad and 5 m (16 ft) cable |
| POL-2ATM | ATM card reader kit: POL-2 reader and programmable timer |
| POL-C1CN | Magnetic stripe card, pre-printed bar code |
| POL-C5CN | Magnetic stripe card, pre-printed bar code, glossy front for dye-sublimation printing |
| POL-C6CN | Magnetic stripe card, glossy front for dye-sublimation printing |

Related Products

