


Versi-Duct® Vertical Cable Management System

APPLICATION

The Versi-Duct Cable Management System uses slotted ducts to route cable. The system mounts onto an industry-standard equipment rack. Two vertical 40-inch ducts, or one 80-inch duct (comprised of two 40-inch ducts) span the full length of a standard seven-foot equipment rack. The horizontal and vertical slotted ducts come with cable concealing covers and an assortment of accessories.



SPECIFICATION

The vertical cable management system shall be in a slotted duct configuration for copper and fiber cable systems. The management system shall be cULus listed, PVC rated for 94V-0, ABS rated for UL94HB, and compliant with ANSI/TIA-568-C standards. It shall mount onto an industry-standard 19-inch equipment rack. The management system shall offer an assortment of accessories, including a bend-radius compliant cable router to transition cable from a horizontal to vertical slotted duct.

WARRANTY INFORMATION

For a copy of Leviton product warranties, visit www.leviton.com/warranty.

ELECTRONIC FILES

For CAD files, typical specs, or technical drawings (.DXF, .DWG), visit www.leviton.com.

FEATURES

- Versatile solution for fiber/copper cable organization and management
- Front only and front/rear configurations
- Cable concealing covers
- Mount on standard equipment racks with top, bottom, and side cable entry
- Finger alignment with rack spacing

DESIGN CONSIDERATIONS

- Use on side of rack to route, protect, and manage fiber or copper cable
- Bend-radius compliant cable router complies with ANSI/TIA standards, ensuring a minimum 1.18-inch bend radius

STANDARDS COMPLIANCE

- ANSI/TIA-568-C
- cULus Listed

PHYSICAL SPECIFICATIONS

Dimensions: See page two
Materials (channel): ABS rated for UL94HB
Materials (cover): PVC rated for UL 94V-0


ACCESSORIES

Accessories sold separately:

- **Cable Retainer** - Mounts on the duct fingers, is adjustable to slide along the duct finger, and includes break-away detail to accommodate all duct sizes
- **Mounting Bracket Kit** - Used to attach a vertical duct to an adjacent equipment rack (each kit comes with #8 screws)
- **Bend-Radius Compliant Cable Router** - Routes copper or fiber cable from inside the horizontal duct to the vertical duct, maintaining a minimum bend radius of 1.18 inches
- **Slack Loop Storage Organizer** - Stores slack cable and maintains a minimum of 1.18-inch bend-radius. Designed to be mounted on the duct fingers and can be adjusted to a variety of slack loop sizes
- **Duct Cover Hinge** - Designed to easily open and close duct cover for increased protection and easy access

COUNTRY OF ORIGIN

Taiwan: 4940L-VF_x, 4980L-VF_x, 49265-BKT
USA: 49265-xxx, 59265-5DC



PART NUMBERS

Description	Part No.
Versi-Duct® Vertical Slotted Duct - 4" x 5" rear and 4" x 5" front (front and rear) 40" H	4940L-VFR
Versi-Duct Vertical Slotted Duct - 4" x 5" (front only) 40" H	4940L-VFO
Versi-Duct Vertical Slotted Duct - 4" x 5" rear and 4x5 front (front and rear) 80" H	4980L-VFR
Versi-Duct Vertical Slotted Duct 4" x 5" (front only) 80" H	4980L-VFO
Versi-Duct Cable Retainer	49265-WR1
Versi-Duct Slack Loop Organizer	49265-SL1
Versi-Duct Slack Loop Organizer (Extended)	49265-SL2
Versi-Duct Mounting Bracket	49265-BKT
Versi-Duct Duct Cover Hinge	49265-HNG
Vertical 40" Designer Cover, 5" channel, grey (set of 2)	59265-5DC



Leviton Network Solutions
 2222 - 222nd St. SE
 Bothell, WA 98021-4416

Asia / Pacific
 T +1.631.812.6228
 E infoasean@leviton.com

Canada
 T +1.514.954.1840
 E pcservice@leviton.com

Caribbean
 T +1.954.593.1896
 E infocaribbean@leviton.com

China
 T +852.2774.9876
 E infochina@leviton.com

Colombia
 T +57.1.743.6045
 E infocolombia@leviton.com

tel 1-800-824-3005
 tel +1-425-486-2222
 appeng@leviton.com
 www.leviton.com

Europe
 T +33.6.8869.1380
 E infoeurope@leviton.com

India / SAARC
 T +971.4.886.4722
 E infoindia@leviton.com

Mexico
 T +52.55.5082.1040
 E lsamarketing@leviton.com

Middle East & Africa
 T +971.4.886.4722
 E lmeinfo@leviton.com

South Korea
 T +82.2.3273.9963
 E infokorea@leviton.com