

RSH Series

custom rackmount

install virtually any component in a standard 19" enclosure; custom cut to provide a perfect opening for the face of the component you are mounting

features:

- Custom cut to provide perfect opening
- Enhanced for superior ventilation
- Assembles easily in minutes
- Rear brackets included to prevent mounted component from sliding back
- Accepts any component up to 17-3/8" wide, iPad and iPod docks
- Choice of finishes: black brushed and anodized and black textured powder coat
- Optional rubber-lined captivating clamps available for use in mobile applications and installations in seismic zones
- Face plates may also be ordered separately (model AFACE, SFACE)
- UL Listed in the US and Canada



specifications:

EIA compliant 19" custom rackmount shall be Middle Atlantic Products model # RSH4(A,S) custom fit to accommodate the component installed in RSH (A- black brushed and anodized, S- textured black powder coat). RSH series custom rackshelf shall be constructed of the following materials: vented bottoms and side panels (ears) shall be steel with a durable flat black powder coat finish, faceplate shall be aluminum. RSH Series custom rackshelf shall have a weight capacity of __lbs. (refer to chart). Custom rackshelf shall be UL Listed in the US and Canada. Clamp kit for RSH series custom rackshelf shall be Middle Atlantic Products part # -C. Clamp kit shall be constructed of steel and finished in a durable black powder coat. Custom rackshelf shall be RoHS EU Directive 2011/65/ EU compliant. Custom rackshelf shall be manufactured by an ISO 9001 and ISO 14001 registered company. Custom rackshelf shall be warranted to be free from defects in material or workmanship under normal use and conditions for the lifetime of the product.

Customizable specification clips available at middleatlantic.com



options:

- Clamp kit for 2 space and greater models to use in mobile applications and installations in seismic zones, part # -C

what **great systems** are built on.™

A brand of **legrand**


Middle Atlantic Products
middleatlantic.com | middleatlantic.ca

96-034 / rev g / 2-7-17

RSH Series

1 RU basic dimensions

all dimensions in inches unless otherwise noted [all dimensions in brackets are in millimeters]



Rackspaces	A Height	B Maximum Equipment Height	C Minimum Equipment Height	Weight Capacity
1 space	1.75 [44]	1.4 [35]	.3 [7]	35 lbs.

Part #	Finish	Bottom Depth	Useable Depth
RSH4A	black brushed and anodized	8.00 [203]	7.6 [193]
RSH4S	black textured powder coat	11.5 [292]	11.1 [282]

what **great systems** are built on.™

A brand of **legrand**


Middle Atlantic Products

middleatlantic.com | middleatlantic.ca




RSH Series

2-12 RU basic dimensions

all dimensions in inches unless otherwise noted [all dimensions in brackets are in millimeters]




side view



Rackspaces	A Height	B Maximum Equipment Height	C Minimum Equipment Height	Weight Capacity
2 space	3.50 [89]	2.85 [72]	1.41 [26]	250 lbs.
3 space	5.25 [133]	4.60 [117]	2.79 [71]	250 lbs.
4 space	7.00 [178]	6.35 [161]	4.54 [115]	250 lbs.
5 space	8.75 [222]	8.10 [206]	6.29 [160]	250 lbs.
6 space	10.50 [267]	9.85 [250]	8.04 [204]	250 lbs.
7 space	12.25 [311]	11.60 [295]	9.79 [249]	250 lbs.
8 space	14.00 [356]	13.35 [339]	11.54 [293]	250 lbs.
9 space	15.75 [400]	15.10 [384]	13.29 [338]	250 lbs.
10 space	17.50 [445]	16.85 [428]	15.04 [382]	250 lbs.
11 space	19.25 [489]	18.60 [472]	16.79 [427]	250 lbs.
12 space	21.00 [533]	20.35 [517]	18.54 [471]	250 lbs.

Part #	Finish	Bottom Depth	Useable Depth
RSH4A	black brushed and anodized	11.50 [292]	11.1 [282]
RSH4S	black textured powder coat	14.00 [356]	13.6 [345]
-C	clamp kit for all above	15.50 [394]	15.1 [384]
AFACE	black anodized face plate only	17.50 [445]	17.1 [434]
SFACE	black textured face plate only	20.50 [521]	20.1 [511]



what **great systems** are built on.™

A brand of **legrand**






Middle Atlantic Products

middleatlantic.com | middleatlantic.ca

RSH Series

iPod® basic dimensions

all dimensions in inches unless otherwise noted [all dimensions in brackets are in millimeters]



what **great systems** are built on.™

A brand of **legrand**

Middle Atlantic Products

middleatlantic.com | middleatlantic.ca