



A Tyco International Company

DSC PowerSeries Keypads



Features that make a difference:

Common to all Keypads:

- Modern, slim-line landscape keypad
- Large, backlit keypad buttons
- 5 programmable function keys
- Programmable Input/Output terminal
- Individual FAP keys
- Multiple door chime per zone
- Adjustable backlight and keypad buzzer
- Wire channel
- Dual wall-mount and front cover tamper
- Easy-to-install mounting hinge
- Surface or single-gang box mount

Security at your Fingertips

PowerSeries high-quality, slim-profile keypads achieve a clean, unobtrusive look that homeowners welcome and installers will appreciate for their easy programming and installation. The keypads feature an input/output terminal that can be programmed to operate as a zone input, programmable output or as a low temperature sensor. The keypads also include adjustable backlit keys that address low-light situations and five programmable keys for simple one button activation of system functions. PK5500/RFK5500 64-zone full-message keypads support eight languages, global partition status and full, 32-character programmable phrases.



PK5500 | RFK5500



PK5508 | RFK5508



PK5501 | RFK5501



PK5516 | RFK5516

Easy To Use

To simplify usage, the keypads feature five programmable keys for easy one-button activation of system functions. The default tasks assigned to the five function keys are stay arming, away arming, door chime, smoke detector reset and quick exit. With the quick exit function there's no need to disarm and rearm the system every time an occupant leaves the house or lets the dog out, for example.

Flexibility

The keypads' integrated temperature sensor can be programmed to activate when room temperature dips below 43° F (6° C) and restores at 47° F (8° C). Built-in logic prevents the panel from cycling in and out of alarm mode during minor temperature fluctuations, helping to reduce false alarms.)

Wireless Convenience

RF versions of the keypads are available. They include all of the same features as their hardwired equivalents and are able to support 32 wireless zones and 16 wireless keys without taking up a wireless zone slot.

Full message LCD Keypad languages supported:

Croatian, Czech, Danish, Dutch, English, Estonian, Finnish, French, German, Greek, Hungarian, Italian, Latvian, Lithuanian, Norwegian, Polish, Portuguese, Slovak, Spanish, Swedish

Compatibility

The keypads are compatible with all PowerSeries control panels.

Specifications

Dimensions.....	6 1/16" x 4 7/16" x 13/16" (154 mm x 113 mm x 20.5 mm)
LCD Viewable Area.....	3 9/10" x 15/16" (99 mm x 24 mm)
Current Draw	125 mA (Max)
Voltage	12 VDC Nominal
Operating Environment	32° to 120° F (0° to 49° C)
Relative Humidity	5 to 93%

Ordering Information:

PK5500	64-Zone Full-Message LCD Keypad
RFK5500	Wireless 64-Zone Full-Message LCD Keypad
PK5501	64-Zone LCD Picture ICON Keypad
RFK5501	Wireless 64-Zone LCD Picture ICON Keypad
PK5516	16-Zone LED Keypad
RFK5516	Wireless 16-Zone LED Keypad
PK5508	8-Zone LED Keypad
RFK5508	Wireless 8-Zone LED Keypad