



## 4-Port USB PS/2 KVM Switch Kit TK-423K

The 4-Port USB PS/2 KVM Switch Kit with Audio (TK-423K) provides control of 4 computers/servers with just one set of console controls.

Manage 4 computers that have open VGA and PS/2 or USB ports at the touch of a button with one set of PS/2 or USB keyboard and mouse, VGA monitor, microphone and speakers.

No need for additional cabling, all required cables are included. Independent audio/mic and PC port selection provide additional flexibility. LED indicators show connection status and a buzzing sound confirms port switching. With Hot-Plug, Auto-Scan and Hot-Key operating features, this versatile device is the perfect choice for managing 4 computers/servers.

### FEATURES


- Manage up to 4 computers/servers with one set of console devices
- All required cabling included
- Cables from the KVM switch to the computers/servers feature VGA and PS/2 connectors
- Supported console connections are as follows: PS/2 or USB keyboard and mouse ports, VGA monitor port and speaker/mic port
- Audio and microphone support
- Audio/mic port selection may be independent of keyboard, video and mouse port selection
- Control computer/server selection with front push buttons and keyboard hotkeys
- Supports Universal Host and Open Host Controller Interface (UHCI/OHCI)
- Multiple platforms supported: Windows 7/Vista/2003 Server/ XP/2000/ME/98SE, Mac OS, Linux and more
- Port switching confirmed by LED status indicators and audio tone
- High quality VGA resolution up to 2048 x 1536
- 2-year limited warranty

# 4-Port USB PS/2 KVM Switch Kit TK-423K

## SPECIFICATIONS

Hardware	
Connection	• 4 computers
PC Port connection	• 4 x VGA HDB 15-pin female • 4 x 3.5mm speaker in/out jack • 4 x 3.5mm microphone in/out jack
Console port connectors	• 2 x USB 1.1 type A for keyboard/ mouse • 1 x PS/2 keyboard 6-pin mini DIN female • 1 x PS/2 mouse 6 pin mini DIN female • 1 x VGA HDB 15 pin female • 1 x 3.5mm speaker in/out jack • 1 x 3.5mm microphone in/out jack
KVM Cables	• 4 x KVM Multiple Connection Cable (2 x 1.2m/4ft., 2 x 1.8m/6ft) • 4 x KVM speaker/Microphone Cable (2 x 1.2m/4ft., 2 x 1.8m/6ft)
Cable Interface	• 1 x VGA 15 pin male to male connector • 1 x USB type A connector • 1 x PS/2 Connector (Keyboard connector) • 1 x USB to PS/2 Gender Connector (Support for PS/2 Mouse)
PC selection	• Hotkey/ push button
LED	• 4 x LED Green
Auto Scan Interval	• Programmable 5-99 seconds
VGA Resolution	• 2048 x 1536
Power Adapter	• 5V DC 2A external power adapter
Dimensions (L x W x H)	• 255 x 117.5 x 45 mm (10.039 x 4.606 x 1.771 inches)
Weight	• 1000 g (35.2 oz.)
Temperature	• 0C° ~ 40C° (32F° ~104F°)
Humidity	• Max 90%, non-condensing
Certifications	• CE, FCC

## NETWORKING SOLUTIONS



## PACKAGE CONTENTS

- TK-423K
- Multi-language quick installation guide
- 4 sets of KVM Multiple Connection Cable (2 x 1.2M/4ft, 2 x 1.8M(6ft.)
- 4 sets of KVM Audio/Microphone Cable (2 x 1.2M/4ft, 2 x 1.8M(6ft.)
- Power adapter (5V DC, 2A)

## RELATED PRODUCTS

TK-401R	4-Port Rack Mount KVM Switch
TK-403KR	4-Port Audio KVM Switch
TK-409K	4-Port USB KVM Switch Kit with Audio

## ORDERING INFORMATION

### TRENDnet®

20675 Manhattan Place, Torrance, CA 90501 USA

Tel: 1-310-961-5500

Fax: 1-310-961-5511

Web: [www.trendnet.com](http://www.trendnet.com)

Email: [sales@trendnet.com](mailto:sales@trendnet.com)

To Order Please Call:

**1-888-326-6061**

