

High-Capacity 8" Versi-Duct® Cable Management System

APPLICATION

A vertical cable management system designed to optimize performance and protect network cabling infrastructure. This high-capacity system provides a simplified solution for the routing of copper and fiber cables and mounts onto any industry standard equipment rack. The new 8" wide channel was built to maximize cable handling capacity while protecting cable integrity in an injected molded product. This vertical management system comes with cable concealing covers and is kitted with accessories to properly manage the installation.



SPECIFICATION

A vertical cable management system designed for copper and fiber cabling systems. The management system shall be cULus listed, PCI rated for 94V-O, ABS rated for UL94HB, and compliant with ANSI/TIA/EIA 568-B standards. Mounting hardware shall be included to insure the proper installation to infrastructure. It shall mount onto a standard TIA/EIA recognized equipment rack. The management system shall offer an assortment of accessories, including a bend radius slack loop organizer and cable retainers.

FEATURES

- Versatile solution for fiber/copper cable organization and management
- Durable ABS plastic channels withstand years of use in demanding environments
- Large finger passthrough space aligns with rack units
- Radius edges protect cable routing
- Front only and front/rear configurations
- Dual hinged, cable concealing covers included
- Channels kitted with cable retainers, slack loop organizers, mounting brackets, and covers
- Accommodates top, bottom, side and pass-through cable routing
- Mount on standard equipment racks

DESIGN CONSIDERATIONS

- Product is comprised of two 40" long sections that span the full length of a standard equipment rack
- Includes mounting brackets intended to secure channel to side of industry standard equipment rack
- Additional mounting brackets may be added for center mounting options between two racks
- Slack loop organizer accommodates 60 lbs of cable

STANDARDS COMPLIANCE

Meets or exceeds all applicable standards: cULus Listed; complies with TIA/EIA-568-B; and meets FCC Part 68

PHYSICAL SPECIFICATIONS

Dimensions: See second page
Materials (channel): ABS rated for UL94HB
Materials (cover): PVC rated for UL94V-0

ACCESSORIES

- **Slack Loop Organizer** – Stores cable slack and maintains proper bend radius for CAT 6A applications. Designed to fit in the center of the channel, it can be mounted in six locations according to the needs of the installation.
- **Cable Retainer** – Mounts on the channel fingers and snaps into multiple positions along the fingers to secure cable bundles.
- **Mounting Brackets** – Additional brackets may be used to center mount channel between two racks.

WARRANTY INFORMATION

For a copy of Leviton product warranties, visit www.leviton.com.

Leviton Network Solutions

2222 - 222nd St. SE
Bothell, WA 98021-4416

tel 1-800-824-3005
tel +1-425-486-2222
appeng@leviton.com
www.leviton.com

Asia / Pacific

T +1.631.812.6228
E infoasean@leviton.com

Europe

T +33.6.8869.1380
E infoeurope@leviton.com

Canada

T +1.514.954.1840
E pcservice@leviton.com

India / SAARC

T +91.80.4322.5678
E infoindia@leviton.com

Caribbean

T +1.954.593.1896
E infocaribbean@leviton.com

Mexico

T +52.55.5082.1040
E lsamarketing@leviton.com

China

T +852.2774.9876
E infochina@leviton.com

Middle East & Africa

T +971.4.886.4722
E imeinfo@leviton.com

Colombia


T +57.1.743.6045
E infocolombia@leviton.com

South Korea


T +82.2.3273.9963
E infokorea@leviton.com

ELECTRONIC FILES


For CAD files, typical specs, or dimensional line art (.DXF, .DWG, MS-DOS.eps or .TXT), visit www.leviton.com.




Vertical Cable Management (front and rear)




Cable Retainer



Mounting Bracket



Slack Loop Organizer



Feature	Channel Depth (WxD)	Area (In ²)	CAT 6A Capacity (.354" Cable)	CAT 6 Capacity (.250" Cable)	CAT 5e Capacity (.180" Cable)
8" channel size (per side)	8" x 8"	60	192	384	738
Finger Spacing	5.5" x 1"	5.5	24	60	114
Large Passthrough	4.8" x 2.6"	12.7	72	120	258
Small Passthrough	2.6" x 2.6"	6.8	36	72	138

VERSI-DUCT® 8" CHANNEL VERTICAL CABLE MANAEGEMENT & ACCESSORIES

Description	Front Only	Front & Rear
Vertical 80" Length, 8"W x 8"D channel w/ standard hinged black cover	8980L-VFO	8980L-VFR
Vertical 80" Length, 8"W x 8"D channel w/ designer hinged grey cover	8C80L-VFO	8C80L-VFR
Vertical Center Mounting Bracket, 8" channel		89265-BKT
Vertical Cable Retainer, 8" channel		89265-WR1
Vertical Slack Loop Organizer, 8" channel		89265-SL1



Leviton Network Solutions
 2222 - 222nd St. SE
 Bothell, WA 98021-4416

Asia / Pacific
 T +1.631.812.6228
 E infoasean@leviton.com

Canada
 T +1.514.954.1840
 E pcservice@leviton.com

Caribbean
 T +1.954.593.1896
 E infocaribbean@leviton.com

China
 T +852.2774.9876
 E infochina@leviton.com

Colombia
 T +57.1.743.6045
 E infocolombia@leviton.com

tel 1-800-824-3005
 tel +1-425-486-2222
 appeng@leviton.com
 www.leviton.com

Europe
 T +33.6.8869.1380
 E infoeurope@leviton.com

India / SAARC
 T +91.80.4322.5678
 E infoindia@leviton.com

Mexico
 T +52.55.5082.1040
 E lsamarketing@leviton.com

Middle East & Africa
 T +971.4.886.4722
 E lmeinfo@leviton.com

South Korea
 T +82.2.3273.9963
 E infokorea@leviton.com