

eXtreme® Cat 6 UTP Patch Cord

APPLICATION

Leviton eXtreme Cat 6 patch cords are designed to be used in typical Cat 6 channel applications. Leviton eXtreme Cat 6 systems are designed for use in high-bandwidth applications such as Gigabit Ethernet.



SPECIFICATION

Patch cords shall meet or exceed requirements for Cat 6 performance described in ANSI/TIA-568-C.2. Patch cords shall be stranded conductor with an 8-position modular plug on each end. The cords shall be available in standard lengths of 1, 3, 5, 7, 10, 15, and 20 feet. Patch cord plug shall be clear and contacts shall have industry-standard, ANSI/TIA-1096-A compliant 50 micro inches of gold plating.

FEATURES

- Stranded conductor for longer flex-life
- T568B wiring to function in either T568A or T568B applications
- Color-matched cords and boots

DESIGN CONSIDERATIONS

- ANSI/TIA channel performance limits the total length of work area and equipment room cords to 32 feet (10 meters) per ANSI/TIA-568-C.2 or 88.6 feet (27 meters) in a MUTOA application
- A variety of colors for color coding and organizing
- Available in six standard lengths
- Color-matched rubber boot provides protection for plug

STANDARDS COMPLIANCE

- ANSI/TIA-568-C.2
- ISO/IEC 11801-B
- ANSI/TIA-1096-A
- cULus Listed
- UL 444 CM rated
- Supports IEEE 802.3af, 802.3at, and Cisco UPoE up to 60 watts
- Supports emerging PoE standards such as the draft IEEE 802.3bt, up to 100 watts; with bundle sizes of 100 cords or less

PERFORMANCE SPECIFICATIONS

Dimensions	See page two
Outer Diameter (O.D.):	0.225"
Materials:	Plug body is high-impact, fire-retardant plastic rated UL 94V-0
Color:	White, Grey, Black, Blue, Red, Yellow, Green (Matching color boots)

COUNTRY OF ORIGIN

China

WARRANTY INFORMATION

For a copy of Leviton product warranties, visit www.leviton.com/warranty.

62460-xx*

Leviton Network Solutions

2222 - 222nd St. SE
Bothell, WA 98021-4416

tel 1-800-824-3005
tel +1-425-486-2222
appeng@leviton.com
www.leviton.com

Asia / Pacific

T +1.631.812.6228
E infoasean@leviton.com

Europe

T +33.6.8869.1380
E infoeurope@leviton.com

Canada

T +1.514.954.1840
E pcservice@leviton.com

India / SAARC

T +971.4.886.4722
E infoindia@leviton.com

Caribbean

T +1.954.593.1896
E infocaribbean@leviton.com

Mexico

T +52.55.5082.1040
E lsamarketing@leviton.com

China

T +852.2774.9876
E infochina@leviton.com

Middle East & Africa

T +971.4.886.4722
E lmeinfo@leviton.com

Colombia


T +57.1.743.6045
E infocolombia@leviton.com

South Korea

T +82.2.3273.9963
E infokorea@leviton.com

ELECTRONIC FILES

For CAD files, typical specs, or technical drawings (.DXF, .DWG), visit www.leviton.com.



62460-xx*

PART NUMBERS

Description	Part No.
Leviton eXtreme® Cat 6 Patch Cord, 1-foot length (0.3 m)	62460-01*
Leviton eXtreme Cat 6 Patch Cord, 3-foot length (0.9 m)	62460-03*
Leviton eXtreme Cat 6 Patch Cord, 5-foot length (1.5 m)	62460-05*
Leviton eXtreme Cat 6 Patch Cord, 7-foot length (2.1 m)	62460-07*
Leviton eXtreme Cat 6 Patch Cord, 10-foot length (3.0 m)	62460-10*
Leviton eXtreme Cat 6 Patch Cord, 15-foot length (4.6 m)	62460-15*
Leviton eXtreme Cat 6 Patch Cord, 20-foot length (6.1 m)	62460-20*

*=Colors: (W) White, (Y) Yellow, (L) Blue, (E) Black, (R) Red, (G) Green, (S) Grey



For assistance customizing your patch cords, please visit www.leviton.com/configurator or call Tech Support at 800.824.3005.



Leviton Network Solutions 2222 - 222nd St. SE Bothell, WA 98021-4416 tel 1-800-824-3005 tel +1-425-486-2222 appeng@leviton.com www.leviton.com	Asia / Pacific T +1.631.812.6228 E infoasean@leviton.com	Canada T +1.514.954.1840 E pcservice@leviton.com	Caribbean T +1.954.593.1896 E infocaribbean@leviton.com	China T +852.2774.9876 E infochina@leviton.com	Colombia T +57.1.743.6045 E infocolombia@leviton.com
	Europe T +33.6.8869.1380 E infoeurope@leviton.com	India / SAARC T +971.4.886.4722 E infoindia@leviton.com	Mexico T +52.55.5082.1040 E lsamarketing@leviton.com	Middle East & Africa T +971.4.886.4722 E lmeinfo@leviton.com	South Korea T +82.2.3273.9963 E infokorea@leviton.com