


eXtreme® Cat 5e SlimLine Boot UTP Patch Cords

5D460-xxx

APPLICATION

Leviton eXtreme SlimLine patch cords feature low-profile strain-relief boots to support today's high-density applications. Patch cords are designed to be used with high-density panels and switches. The snagless design makes SlimLine patch cords an excellent choice in environments with frequent moves, adds, and changes.



FEATURES

- Independently tested and verified by Intertek (ETL) for Cat 5e component performance
- Improved plug access in tight spaces
- Snagless plug design
- Stranded conductor for longer flex-life
- Improved strain relief

DESIGN CONSIDERATIONS

- ANSI/TIA channel performance limits total length of patching and equipment cords to 32 feet (10 meters) per ANSI/TIA-568-C.2
- A variety of colors for color coding or organization
- Available in four standard lengths (custom lengths also available)

STANDARDS COMPLIANCE

- ANSI/TIA-568-C.2
- ISO/IEC 11801
- ANSI/TIA-1096-A (formerly FCC Part 68)
- cULus Listed
- RoHS
- UL 444 CM rated
- IEEE 802.3at (Type 1) PoE up to 15.4 watts
- IEEE 802.3at (Type 2) PoE+ up to 30 watts
- IEEE Draft 802.3bt (Type 3) PoE+ up to 60 watts
- Cisco Universal Power Over Ethernet (UPOE) up to 60 watts

SPECIFICATION

Patch cords shall meet or exceed requirements for Cat 5e performance described in ANSI/TIA-568-C.2. Patch cords shall be stranded conductor with an 8-position modular plug on each end. The cords shall be available in lengths of 3, 5, 7, and 10 feet. Patch cords shall include a narrow-profile boot and a snag-free latch. Patch cord plug shall have industry-standard, ANSI/TIA-1096-A compliant 50 micro inches of gold plating.

COUNTRY OF ORIGIN

China

PHYSICAL SPECIFICATIONS

Dimensions: See page two
Outer Diameter (O.D.): 0.22"
Materials: 24-gauge, UTP stranded conductor, modular non-keyed, 8-position, 8-conductor plug, 94V-0 rated
Colors: White, yellow, blue, green, grey

WARRANTY INFORMATION

Limited Product and Limited Extended Warranties are rendered VOID if the installed structured cabling system is used for PoE applications that exceed the product's specified power rating. For a copy of Leviton product warranties, visit www.leviton.com/warranty.

Leviton Network Solutions

2222 - 222nd St. SE
Bothell, WA 98021-4416

tel 1-800-824-3005
tel +1-425-486-2222
appeng@leviton.com
www.leviton.com

Asia / Pacific

T +1.631.812.6228
E infoasean@leviton.com

Europe

T +44.0.1592.772124
E customerservice@brand-rex.com

Canada

T +1.514.954.1840
E pcservice@leviton.com

India / SAARC

T +971.4.886.4722
E infoindia@leviton.com

Caribbean

T +1.954.593.1896
E infocaribbean@leviton.com

Mexico

T +52.55.5082.1040
E lsamarketing@leviton.com

China

T +852.2774.9876
E infochina@leviton.com

Middle East & Africa

T +971.4.886.4722
E lmeinfo@leviton.com

Colombia


T +57.1.743.6045
E infocolombia@leviton.com

South Korea

T +82.2.3273.9963
E infokorea@leviton.com

ELECTRONIC FILES

For CAD files, typical specs, or technical drawings (.DXF, .DWG), visit www.leviton.com.



5D460-XXX

PART NUMBERS

Description	Part No.
eXtreme® Cat 5e SlimLine Boot UTP Patch Cord, 3-foot length (0.9 m)	5D460-03*
eXtreme Cat 5e SlimLine Boot UTP Patch Cord, 5-foot length (1.5 m)	5D460-05*
eXtreme Cat 5e SlimLine Boot UTP Patch Cord, 7-foot length (2.1 m)	5D460-07*
eXtreme Cat 5e SlimLine Boot UTP Patch Cord, 10-foot length (3.0 m)	5D460-10*

* = Colors: White (W), Yellow (Y), Blue (L), Green (G), Grey (S)



For assistance customizing your patch cords, please visit www.leviton.com/configurator or call Tech Support at 800.824.3005.



Leviton Network Solutions 2222 - 222nd St. SE Bothell, WA 98021-4416	Asia / Pacific T +1.631.812.6228 E infoasean@leviton.com	Canada T +1.514.954.1840 E pcservice@leviton.com	Caribbean T +1.954.593.1896 E infocaribbean@leviton.com	China T +852.2774.9876 E infochina@leviton.com	Colombia T +57.1.743.6045 E infocolombia@leviton.com
tel 1-800-824-3005 tel +1-425-486-2222 appeng@leviton.com www.leviton.com	Europe T +44.0.1592.772124 E customerservice@brand-rex.com	India / SAARC T +971.4.886.4722 E infoindia@leviton.com	Mexico T +52.55.5082.1040 E lsamarketing@leviton.com	Middle East & Africa T +971.4.886.4722 E lmeinfo@leviton.com	South Korea T +82.2.3273.9963 E infokorea@leviton.com