

Single-Gang QuickPort® Wallplates

APPLICATION

Single-Gang QuickPort Wallplates accept QuickPort connectors to support multimedia applications with 1, 2, 3, 4, or 6 ports. Use where a one-piece, single-gang, economical flush-mount housing is desired. Available in six colors (white, light almond, ivory, grey, brown, and black) with color-matched screws.



SPECIFICATION

The wallplate housing shall be a one-piece, single-gang flush-mount style that fits standard NEMA openings, or four-square boxes with reducer. It should provide 1, 2, 3, 4, or 6 ports. Must be able to accept all Leviton QuickPort connectors. It must be made of high-impact, fire-retardant plastic rated UL 94V-0, and be cULus Listed, and compliant with ANSI/TIA-568-C.0 specifications. The wallplate shall accommodate low-voltage box eliminators for a flush mount.

FEATURES

- Color-matched wallplate screws
- Fits within minimum rectangular NEMA openings and accommodates low-voltage box eliminators for a flush mount
- Compatible with all individual QuickPort connectors
- Individual port configurability allows specification flexibility
- Narrow module width allows high port density in a small area

DESIGN CONSIDERATIONS

- Fits single-gang back boxes, or four-square boxes with appropriate user-provided reducer
- Put blanks in unused ports for future expansion
- Specify port identification method (colored modules, designation labels, and custom silk-screening available to identify ports, use different colored connectors for each application or Leviton pre-printed Port Designation Labels (41080-LEB)

STANDARDS COMPLIANCE

- cULus Listed (UL 1863 & CAN/CSA-C22.2 No. 182.4)
- ANSI/TIA-568-C.0

PHYSICAL SPECIFICATIONS

Dimensions:	See page two
Materials:	High-impact, durable, fire-retardant plastic rated UL 94V-0
Capacity:	Available in 1-, 2-, 3-, 4-, and 6-port versions
Mounting:	Color-matched screws

COUNTRY OF ORIGIN

USA


WARRANTY INFORMATION

For a copy of Leviton product warranties, visit www.leviton.com/warranty.

41080-xxP

ELECTRONIC FILES

For CAD files, typical specs, or technical drawings (.DXF, .DWG), visit www.leviton.com.



PART NUMBERS

Description	WHITE	LT. ALMOND	IVORY	GREY	BROWN	BLACK
Single-Gang QuickPort® Wallplate, 1 Port	41080-1WP	41080-1TP	41080-1IP	41080-1GP	41080-1BP	41080-1EP
Single-Gang QuickPort Wallplate, 2 Ports	41080-2WP	41080-2TP	41080-2IP	41080-2GP	41080-2BP	41080-2EP
Single-Gang QuickPort Wallplate, 3 Ports	41080-3WP	41080-3TP	41080-3IP	41080-3GP	41080-3BP	41080-3EP
Single-Gang QuickPort Wallplate, 4 Ports	41080-4WP	41080-4TP	41080-4IP	41080-4GP	41080-4BP	41080-4EP
Single-Gang QuickPort Wallplate, 6 Ports	41080-6WP	41080-6TP	41080-6IP	41080-6GP	41080-6BP	41080-6EP

