

Metal Splice Trays

APPLICATION

Splice Trays provide complete protection for delicate stripped fibers and splices for all types of fiber cable designs. All trays accommodate a wide variety of splice holders and feature a clear polycarbonate cover for viewing of tray contents. Central and offset mounting holes are protected by a spacer block which prevents fiber damage during installation and removal.



SPECIFICATION

The fiber splice trays shall be offered in 4-inch and 5-inch widths with clear polycarbonate covers for viewing, and tie-down holes for securing incoming fiber. The trays shall accommodate heat shrink, bare fusion, or ribbon-style splicing for both single-mode and multimode fiber and a variety of splice holders. Central and offset mounting holes with spacer blocks for fiber protection shall be included.

FEATURES

- Available in four-inch and five-inch widths
- Clear polycarbonate covers
- Tie-down holes for securing incoming fibers
- 12-fiber and 24-fiber high-density versions
- Choose from heat shrink, bare fusion, or ribbon-style splice trays
- Central and offset mounting holes for installation in enclosures
- Mounting hole spacer block creates a protected path to avoid fiber damage during installation and removal
- 4 x 7 inch trays compatible with applicable SDX enclosures
- Compatible with LightSpace® enclosures

DESIGN CONSIDERATIONS

- Splice holders and splice trays sold separately
- Splice trays are stackable
- Use for single-mode or multimode 900 µm or 250 µm fiber
- Mounting hardware and tie wraps are not included

PHYSICAL SPECIFICATIONS

Dimensions: See page two
Material: Tray is aluminum
Cover is clear polycarbonate

COUNTRY OF ORIGIN

USA


WARRANTY INFORMATION

For a copy of Leviton product warranties, visit www.leviton.com/warranty.


ELECTRONIC FILES

For CAD files, typical specs, or technical drawings (.DXF, .DWG), visit www.leviton.com.

4" Splice Trays



5" Splice Trays



T4XXX-XXX, T5XXX-XXX, T6XRB-40Q, 5T000-00T

4" & 5" Metal Splice Trays

Description	Heat Shrink (Plastic)	Heat Shrink (Foam)	Bare Fusion
12-fiber Mini, 4" W x 7" L x 0.32" H	T47HS-P06	—	T47BF-P06 [^]
12-fiber Mini, with standoff 4" W x 7" L x 0.57" H	5T000-00T	—	—
12-fiber Standard, 4" W x 11.75" L x 0.32" H	T4LHS-P06	T4LHS-F06 [^]	T4LBF-P06
24-fiber High Density, 4" W x 11.75" L x 0.32" H	T4LHS-P12	T4LHS-F12 [^]	T4LBF-P12
12-fiber Standard, 5" W x 11.75" L x 0.32" H	T5LHS-P06	T5LHS-F06 [^]	T5LBF-P06
24-fiber High Density, 5" W x 11.75" L x 0.32" H	T5LHS-B12	T5LHS-F12	T5LBF-P12 [^]

Ribbon Style Splice Tray

Description	Part No.
72-fiber Ribbon Style, quartz, 5" W x 10" L x 0.33" H	T6XRB-40Q

Splice Tray Mounting Hardware

Description	Part No.
Splice Tray Mounting-Hardware Kit	SPLMT-HKT

[^] = Minimum order quantity and lead times may apply.



Leviton Network Solutions
 2222 - 222nd St. SE
 Bothell, WA 98021-4416

Asia / Pacific
 T +1.631.812.6228
 E infoasean@leviton.com

Canada
 T +1.514.954.1840
 E pcservice@leviton.com

Caribbean
 T +1.954.593.1896
 E infocaribbean@leviton.com

China
 T +852.2774.9876
 E infochina@leviton.com

Colombia
 T +57.1.743.6045
 E infocolombia@leviton.com

tel 1-800-824-3005
 tel +1-425-486-2222
 appeng@leviton.com
 www.leviton.com

Europe
 T +33.6.8869.1380
 E infoeurope@leviton.com

India / SAARC
 T +971.4.886.4722
 E infoindia@leviton.com

Mexico
 T +52.55.5082.1040
 E lsamarketing@leviton.com

Middle East & Africa
 T +971.4.886.4722
 E lmeinfo@leviton.com

South Korea
 T +82.2.3273.9963
 E infokorea@leviton.com