

## QuickPort® Modular Furniture Products

### APPLICATION

Leviton QuickPort Modular Furniture Faceplates with ID windows feature a designation window for a simple, more organized workstation identification. The faceplates accept QuickPort snap-in connectors and adapters to support a variety of voice/data applications in office environments.

### SPECIFICATION

#### Modular Furniture Faceplate — Standard

Modular furniture connector housing must be a field-configurable faceplate providing from one to four flush-mount ports for a variety of snap-in connectors and adapters.

#### Modular Furniture Faceplate — Herman Miller

Modular furniture connector housing must be a field-configurable flush-mount faceplate compatible with Herman Miller openings, and provide from one to four flush-mount ports for a variety of snap-in connectors and adapters.

#### Modular Furniture Faceplate — Extended Depth

Modular furniture connector housing must be a field-configurable faceplate extending 0.75 inch from the furniture raceway to facilitate fiber or copper cable bend-radius compliance, or to compensate for shallow/powered raceway channels, and provide from one to four flush-mount ports for a variety of snap-in connectors and adapters.

The faceplate must have a rattle-free fit and a single toolless release latch; be constructed of high-impact self-extinguishing plastic rated UL 94V-0; and be cULus Listed, and compliant with ANSI/TIA-568-C.0 specifications.

### FEATURES

- Faceplates accept Leviton QuickPort snap-in connectors, including component-rated CAT 5e, CAT 6, and CAT 6A connectors
- Provides for work area commercial-grade telephone and data patching
- Compact design
- Meets ANSI/TIA-568-C.0 bend-radius requirements
- ID designation window included



49910-xxx

### DESIGN CONSIDERATIONS

- Specify 49910-Sxx (standard) or 49910-Hxx (Herman Miller) versions (dependent on furniture type)\*
- Specify 49910-Exx (same opening size as 49910-Sxx) for installation into shallow raceway channels (plate has 0.5-inch added depth)
- Specify port identification method (colored connectors, adapters, and designation labels available)
- Configure 1, 2, 3, or 4 active ports; spare ports can be filled with blanks for later use (one blank QuickPort insert is included with 4-port plate).

\* xx = various configurations and colors, see page two.

### STANDARDS COMPLIANCE

- cULus Listed (UL 1863 & CAN/CSA-C22.2 No. 182.4)
- ANSI/TIA-568-C.0

### PHYSICAL SPECIFICATIONS

Dimensions: See page two

Materials: Bracket, ABS plastic, rated per UL 94V-0

### COUNTRY OF ORIGIN


Mexico

### WARRANTY INFORMATION

For a copy of Leviton product warranties, visit [www.leviton.com/warranty](http://www.leviton.com/warranty).

## ELECTRONIC FILES

For CAD files, typical specs, or technical drawings (.DXF, .DWG), visit [www.leviton.com](http://www.leviton.com).



49910-xxx

## MODULAR FURNITURE FACEPLATES

Description	WHITE	IVORY	GREY	BLACK
QuickPort® Modular Furniture Faceplate, 2 ports	49910-SW2	49910-SI2	49910-SG2	49910-SE2
QuickPort Modular Furniture Faceplate, 4 ports	49910-SW4	49910-SI4	49910-SG4	49910-SE4
QuickPort Modular Furniture Faceplate, 4 port, extended depth	49910-EW4	49910-EI4	49910-EG4	49910-EE4
QuickPort Modular Furniture Faceplate, 2 ports, Herman Miller	49910-HW2	49910-HI2	49910-HG2	49910-HE2
QuickPort Modular Furniture Faceplate, 4 ports, Herman Miller	49910-HW4	49910-HI4	49910-HG4	49910-HE4

Standard Modular Furniture Faceplates above fit openings of approximately 1.38" x 2.63".

4-port extended depth faceplate provides 0.5-inch added depth (0.75 inch total) for installation into shallow raceway channels, e.g., some powered channels.

Herman Miller faceplates above fit openings of approximately 1.88" x 2.98".

Standard and extended depth faceplates are compatible when used with Herman Miller G1189A Reducer available from Herman Miller dealers.

ID label and window kit included.

