


8-Button Control Panel Wallplate

APPLICATION

Control HDMI® and VGA audiovisual systems with the 8-button Control Panel Wallplate. The panel is ideal for mounting in classrooms and conference rooms to replace or augment remote controls. It has pre-configured buttons for display or projector on/off, volume up/down, and source selection. Buttons can be set up in minutes using the display or projector remote. The panel complements the Leviton HDMI and VGA Autoswitching HDBaseT Extender Wallplate (41920-HRC). It is powered by and communicates with the Autoswitching Wallplate via category cable.



SPECIFICATION

The control panel wallplate shall have eight configurable buttons and fit in a dual-gang form factor. It shall be all-metal construction and have a matte anodized aluminum finish. The buttons shall be pre-configured for power on/off, volume up/down, HDMI 1, HDMI 2, VGA, and lock. Setup shall be via IR learning and include a copy/paste function to expedite setup of multiple rooms for larger projects. Installation shall not require additional computer hardware, Internet access, or software. Control panel shall include a key lock function to reduce inadvertent operation in the field. Volume buttons shall operate by both single press and press/hold.

FEATURES

- Dual-gang form factor with matte anodized aluminum finish
- Rugged all-metal construction
- Pre-configured buttons integrate with Leviton HDMI and VGA Autoswitching HDBaseT Extender Wallplate (41920-HRC):
 - Power on (IR setup required)
 - Power off (IR setup required)
 - Volume up (IR setup required)
 - Volume down (IR setup required)
 - HDMI 1
 - HDMI 2
 - VGA
 - Lock
- Simple setup with IR learning and single twisted-pair cable connection

DESIGN CONSIDERATIONS

- Use with Leviton 41920-HRC HDMI and VGA Autoswitching HDBaseT Extender Wallplate, 41920-HTR HDBaseT certified receiver, and 41920-A01 or 41920-A70 mixing audio amplifier for a complete control and sound reinforcement system
- Power and communication via single category cable from 41920-HRC
- Maximum cable distance between control panel and autoswitching extender wallplate is 70 meters (230 feet)
- Use 41920-K00 control panel set-up kit for configuration of buttons using IR learning and for duplication of button configuration for multiple rooms
- Fits standard NEMA 2-gang opening, minimum 4" square box

STANDARDS COMPLIANCE

- CE, FCC

PHYSICAL SPECIFICATIONS

Dimensions:	114.3 mm W x 114.3 mm H x 28 mm D 4.5" W x 4.5" H x 1.1" D
Materials:	Metal enclosure
Temperature	0° C to 50° C (32° F to 122° F)

COUNTRY OF ORIGIN

China

WARRANTY INFORMATION

For a copy of Leviton product warranties, visit www.leviton.com/warranty.

Leviton Network Solutions

2222 - 222nd St. SE
Bothell, WA 98021-4416

tel 1-800-824-3005
tel +1-425-486-2222
appeng@leviton.com
www.leviton.com

Asia / Pacific

T +1.631.812.6228
E infoasean@leviton.com

Europe

T +44.0.1592.772124
E customerserviceeu@leviton.com

Canada

T +1.514.954.1840
E pcservice@leviton.com

India / SAARC

T +971.4.886.4722
E infoindia@leviton.com

Caribbean

T +1.954.593.1896
E infocaribbean@leviton.com

Mexico

T +52.55.5082.1040
E lsamarketing@leviton.com

China

T +852.2774.9876
E infochina@leviton.com

Middle East & Africa

T +971.4.886.4722
E lmeinfo@leviton.com

Colombia


T +57.1.743.6045
E infocolombia@leviton.com

South Korea


T +82.2.3273.9963
E infokorea@leviton.com

ELECTRONIC FILES

For CAD files, typical specs, or technical drawings (.DXF, .DWG), visit www.leviton.com.



41920-CP8



The Control Panel Adapter Cable (included with wallplate) connects to the Autoswitching Wallplate (41920-HRC, sold separately) over category cable.

PART NUMBER	
Description	Part No.
8-Button Control Panel	41920-CP8



Leviton Network Solutions 2222 - 222nd St. SE Bothell, WA 98021-4416 tel 1-800-824-3005 tel +1-425-486-2222 appeng@leviton.com www.leviton.com	Asia / Pacific T +1.631.812.6228 E infoasean@leviton.com	Canada T +1.514.954.1840 E pcservice@leviton.com	Caribbean T +1.954.593.1896 E infocaribbean@leviton.com	China T +852.2774.9876 E infochina@leviton.com	Colombia T +57.1.743.6045 E infocolombia@leviton.com
	Europe T +44.0.1592.772124 E customerserviceeu@leviton.com	India / SAARC T +971.4.886.4722 E infoindia@leviton.com	Mexico T +52.55.5082.1040 E lsamarketing@leviton.com	Middle East & Africa T +971.4.886.4722 E lmeinfo@leviton.com	South Korea T +82.2.3273.9963 E infokorea@leviton.com