


PANDUIT PART NUMBER	CONDUCTOR SIZE	STUD SIZE	OVERALL LENGTH "A" +/- .12	BARREL LENGTH "B" MIN	BARREL		TONGUE WIDTH "W" +/- .06	TONGUE THICKNESS "T" +/- .02	TONGUE LENGTH "P" MIN	HOLE OFFSET "G" +/- .03	STUD HOLE DIA "D" +/- .02	WRENCH CLEARANCE "C" REF	WIRE STRIP LENGTH	PANDUIT DIE COLOR CODE PANDUIT DIE INDEX NUMBER (BURNDY DIE INDEX NUMBER)
					I.D. +/- .01	O.D. +/- .01								
LAA6-14-X LAA6-56-X	#6 AWG	1/4" 5/16"	2.22	0.81	0.20	0.34	0.55	0.11	0.88	0.44	0.28 0.34	0.44	1"	GRAY DIE P29 (346)
LAA4-14-X LAA4-56-X LAA4-38-X	#4 AWG	1/4" 5/16" 3/8"	2.32	0.88	0.27	0.47	0.66	0.17	1.00	0.44	0.28 0.34 0.41	0.56	1-1/16"	GREEN DIE P37 (375)
LAA2-14-X LAA2-56-X LAA2-38-X	#2 AWG	1/4" 5/16" 3/8"	2.63	1.00	0.31	0.53	0.79	0.17	1.12	0.44	0.28 0.34 0.41	0.68	1"	PINK DIE P42 (348)
LAA1-14-X LAA1-56-X LAA1-38-X	#1 AWG	1/4" 5/16" 3/8"	2.63	1.00	0.35	0.53	0.75	0.17	1.12	0.44	0.28 0.34 0.41	0.68	1"	GOLD DIE P45 (471)
LAA1/0-56-X LAA1/0-38-X LAA1/0-12-X	#1/0 AWG	5/16" 3/8" 1/2"	3.22	1.25	0.39	0.64	0.88	0.25	1.25	0.63	0.34 0.41 0.53	0.62	1-9/16"	TAN DIE P50 (296)

NOTES:

1. MATERIAL: SEAMLESS ALUMINUM TUBING, TIN PLATED
2. BARREL COLOR CODED WITH DIE SET INDEX NUMBER
3. FOR STRANDED ALUMINUM AND COPPER WIRE
4. UL LISTED & CSA CERTIFIED TEMPERATURE RATED 90° C (AL9CU)
5. UL LISTED & CSA CERTIFIED VOLTAGE RATING 35 KV
6. ALL DIMENSIONS IN INCHES



							TITLE
06	12/15	JHNU	JHNU	RGB	REVISED A DIM FOR LAA6: 2.22 WAS 2.19 REVISED A DIM FOR LAA4: 2.32 WAS 2.22 REVISED A DIM FOR LAA1: 2.63 WAS 2.56 REVISED A DIM FOR LAA1/0: 3.22 WAS 3.23	N41203BA-C41203	LAA SERIES #6-1/0 ALUMINUM LUGS CUSTOMER DRAWING
05	8/15	JHNU	JHNU	RGB	ADDED "D" DIMENSION	N41203BA-C41203	ITEM REVISION NAME N41203BA-C41203/06 DATASET FILE NAME C41203/06.SLDDRW
04	3/15	JHNU	JHNU	RGB	REVISED DIMENSIONS REVISED NOTES ADDED BARREL MARKING ADDED COLOR CODE/DIE INDEX NUMBER	N41203BA-C41203	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XXX ± .XX ± ANGLES ±
03	10/14	JHNU	JHNU	RGB	REVISED I.D. FOR LAA1: .35 WAS .31	N41203BA-C41203	THIRD ANGLE PROJECTION
02	3/13	JHNU	JHNU	RGB	REVISED TITLE BLOCK CONVERTED TO SOLIDWOKRS	N41203BA-C41203	DRAWN BY TSM DATE 9/96 CHK SCALE NONE
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	MATERIAL SEE NOTES DRAWING NUMBER C41203 SHEET 1 OF 1 SIZE B