



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

DUPLEX SC TO SC FIBER OPTIC PATCH CORD							
PANDUIT PART NO.	CABLE				SC CONNECTOR		
	RATING	FIBER TYPE	COUNT	COLOR	MAX. IL	MIN. RL	BOOT COLOR
F5PD3-3M*	PLENUM (OFNP)	50/125um	DUPLEX 3.0mm ZIPCORD	ORANGE	0.25dB	20dB	BLACK
F6PD3-3M*		62.5/125um					ELECTRIC IVORY
FXP3-3M*		10GbE OM3		AQUA	0.25dB	26dB	AQUA
FXOP3-3M*		OPTIMIZED 10GbE OM3			0.15dB	26dB	
FZPD3-3M*		10GbE OM4		AQUA	0.25dB	26dB	AQUA
FZOP3-3M*		OPTIMIZED 10GbE OM4			0.15dB	26dB	
F9PD3-3M*		9/125um OS1		YELLOW	0.50dB	55dB	BLUE

* - DENOTES PATCH CORD LENGTH, WHERE M = METERS AND F = FEET



REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
01	09-09-09	EFK		RELEASED TO PRODUCTION	02779-09				

		PANDUIT TM CORP. TINLEY PARK, ILL 60477	
 THIRD ANGLE PROJECTION		ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03 (.XXX) ±.010 (.3) ±.005 ANGLES	
DRAWN BY MC		REVIEW DRAWING NUMBERS	
DATE 04-27-07		DRAWING FILENAME M02779BA_DC/00B	
CHK'D RAF		SCALE NONE	
		PART NO. SEE SHEET 2, 3 & 4	
		DRAWING NO. 02779-09	
		SHEET 3 OF 4	
		SIZE A	

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

DUPLEX SC TO SC FIBER OPTIC PATCH CORD							
PANDUIT PART NO.	CABLE				SC CONNECTOR		
	RATING	FIBER TYPE	COUNT	COLOR	MAX. IL	MIN. RL	BOOT COLOR
F5LD3-3M*	LOW SMOKE ZERO HALOGEN (LSZH) IEC	50/125um	DUPLEX 3.0mm ZIPCORD	ORANGE	0.25dB	20dB	BLACK
F6LD3-3M*		62.5/125um					ELECTRIC IVORY
FXLD3-3M*		10GbE OM3		AQUA	0.25dB	26dB	AQUA
FXOLD3-3M*		OPTIMIZED 10GbE OM3			0.15dB	26dB	
FZLD3-3M*		10GbE OM4		AQUA	0.25dB	26dB	AQUA
FZOLD3-3M*		OPTIMIZED 10GbE OM4			0.15dB	26dB	
F9LD3-3M*		9/125um OS1		YELLOW	0.50dB	55dB	BLUE

* - DENOTES PATCH CORD LENGTH, WHERE M = METERS AND F = FEET

										FIBER OPTIC PATCH CORD DUPLEX SC TO SC CONFIGURATION CUSTOMER DRAWING					
										 PANDUIT ™ CORP. TINLEY PARK, ILL 60477					
										 THIRD ANGLE PROJECTION		ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03 (.XXX) ±.010 (0.3) ±.010 ANGLES		DRAWING FILENAME M02779BA_DC/00B	
										DRAWN BY MC		REVIEW DRAWING NUMBERS		SCALE NONE	
										DATE 04-27-07		PART NO. SEE SHEET 2, 3 & 4		DRAWING NO. 02779-09	
01	09-09-09	EFK		RELEASED TO PRODUCTION	02779-09						CHK'D	RAF	SHEET 4 OF 4		SIZE A
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH						