




PANDUIT
PART NUMBER

WEIGHT

FR12TB58
FR12TB58M2.93 LB/EACH
(1331g/EACH)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE PACKAGE QUANTITY.
2. THE FIBERRUNNER 12x4 QUIKLOCK TRAPEZE BRACKET IS USED TO SUPPORT THE FIBERRUNNER 12x4 CABLE ROUTING SYSTEM BETWEEN TWO (2) SECTIONS OF NEW OR EXISTING 5/8" (M16) THREADED ROD THAT ARE 18" (457.2mm) - 20" (508mm) APART.
3. THE FIBERRUNNER 12x4 QUIKLOCK TRAPEZE BRACKET INCLUDES:
 ONE (1) BRACKET ASSEMBLY,
 FOUR (4) 5/8 HELICAL SPRING LOCKWASHERS,
 FOUR (4) 5/8-11 HEAVY HEX NUTS (FR12TB58 ONLY),
 FOUR (4) M16x2 HEX NUTS (FR12TB58M ONLY),
 ONE (1) 1/4-20 T-BOLT,
 ONE (1) 1/4-20 HEX KEPS NUT
4. FINISH COLOR: BLACK (EXCEPT FOR HARDWARE).
5. DIMENSIONS IN PARENTHESES ARE IN METRIC.



ENG. REF.: D38022CP_DC_FR12TB58_02.prt

CAD FILENAME/LAYERS



FR12TB58.pdf

PANDUIT

CORP TINLEY PARK, ILLINOIS

FIBERRUNNER 12x4 QUIKLOCK TRAPEZE
BRACKET - 5/8" (M16) THREADED ROD
(FR12TB58, FR12TB58M)
CUSTOMER DRAWINGUNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:(.X) ± (.XXX) ±
(.XX) ± .03 (.8) ANGLES ±UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN IN
INCHES, THIRD ANGLE PROJECTION.

DRAWN BY

MAT'L:

JHNU

DATE

10-2-01

CHK'D

RPA

STEEL

SCALE

NONE

DRAWING NO.

38022-50

DWG

A
SIZE

2	8-1-06	DTP	RN	H. REVISED PART WEIGHT. G. REVISED GENERAL NOTE #3.	38022-50	RN	RN		
-	-----	---	---	F. REMOVED ALL REFERENCES TO PART NUMBER FR12TB12.	-----	--	--		
-	-----	---	---	E. REVISED ENTIRE DRAWING TO INCLUDE FR12TB58M.	-----	--	--		
-	-----	---	---	D. REVISED GENERAL NOTES. C. REVISED CHART.	-----	--	--		
1	1-12-05	MSO	RPA	B. REVISED DRAWING TITLE. A. REVISED CAD FILENAME.	38022-50	RN	RN		
R	10-2-01	JHNU	RPA	RELEASED TO PRODUCTION	38022-50	HIW	HIW		
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	GMBH