


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

|                                                      |                                                                                                                                                            |
|------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Material                                             | High Conductivity<br>Seamless Copper Tube                                                                                                                  |
| Plating                                              | Electro-Tin                                                                                                                                                |
| Wire Size                                            | 6 STR/FLEX                                                                                                                                                 |
| Wire Type                                            | Stranded Copper: Class B & C,<br>Compact, Class G, H, I, K, M,<br>Locomotive                                                                               |
| Wire Strip Length                                    | 9/16 in.                                                                                                                                                   |
| Stud Size                                            | 1/4 in.                                                                                                                                                    |
| UL Listed Wire<br>Connector                          | Yes, for applications up to 35kv.<br>Consult cable manufacturer for<br>voltage stress relief instructions<br>with applications greater than<br>2000 volts. |
| UL Temperature<br>Rating                             | 90° C                                                                                                                                                      |
| C.S.A Certified<br>Wire Connector                    | Yes                                                                                                                                                        |
| Panduit Color Code<br>on Barrel                      | BLUE                                                                                                                                                       |
| Panduit Die Index No.<br>on Barrel                   | P24                                                                                                                                                        |
| Alternate Industry<br>Die Index No. ( )<br>on Barrel | (7)                                                                                                                                                        |



LISTED  
Wire Connector



|            |             |           |            |                                      |            |                                                                                                                                  |                                                |
|------------|-------------|-----------|------------|--------------------------------------|------------|----------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------|
|            |             |           |            |                                      |            |  <b>PANDUIT CORP. TINLEY PARK, ILLINOIS</b> |                                                |
|            |             |           |            |                                      |            | LCDX6-14D-L<br>Copper Lug - Two-Hole, Standard Flex Barrel                                                                       |                                                |
| 01         | 7/03        | TLCO      | TLCO       | REMOVED PANDUIT FROM BARREL MARKINGS | 10918      |                                                                                                                                  |                                                |
| <b>REV</b> | <b>DATE</b> | <b>BY</b> | <b>CHK</b> | <b>DESCRIPTION</b>                   | <b>ECN</b> | <b>SCALE</b><br>N/A                                                                                                              | <b>DRAWING NO / CAD FILE</b><br>LCDX6-14D-CUST |