



760031021 | MODG2-12LC-MM-PT
G2 Modular Cassette with 12 LC OptiSPEED® Multimode Pigtails

OBSOLETE

Replaced By

760109488
360G2 Cassette 12-LC-MM-BG-Pigtails SYSTIMAX 360G2 Cassette 12 LC OptiSPEED® Beige with Pigtails iPatch Ready

Product Classification

Portfolio	SYSTIMAX®
Brand	OptiSPEED®
Product Type	Fiber cassette with pigtails
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Type	OM1
Total Fibers, quantity	12

Dimensions

Depth	119.38 mm 4.70 in
Height	30.48 mm 1.20 in
Pigtail Length	1.5 m 4.9 ft
Width	91.44 mm 3.60 in

Environmental Specifications

Safety Standard	UL
-----------------	----

General Specifications

Interface, front	LC
Adapter Color	Beige
Brand	SYSTIMAX®
Interface Feature, front	Standard
Package Quantity	1
Total Ports, quantity, front	12

Optical Performance

Insertion Loss, typical	0.20 dB
Return Loss, minimum	20.0 dB

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

Included Products

- 860278498 (Product Component—not orderable) — OptiSPEED® LC 0.9 mm Pigtail, blue, 1.5 m
- 760099317 | X-TB-6F-BL-F/G (Product Component—not orderable) — OptiSPEED® 900µm Tight Buffered Fiber
 - 460125271 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, multimode
- 860278506 (Product Component—not orderable) — OptiSPEED® LC 0.9 mm Pigtail, orange, 1.5 m
- 760099325 | X-TB-6F-OR-F/G (Product Component—not orderable) — OptiSPEED® 900µm Tight Buffered Fiber
 - 460125271 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, multimode
- 860278514 (Product Component—not orderable) — OptiSPEED® LC 0.9 mm Pigtail, green, 1.5 m
- 760099333 | X-TB-6F-GR-F/G (Product Component—not orderable) — OptiSPEED® 900µm Tight Buffered Fiber
 - 460125271 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, multimode
- 860278522 (Product Component—not orderable) — OptiSPEED® LC 0.9 mm Pigtail, brown, 1.5 m
- 760099341 | X-TB-6F-BR-F/G (Product Component—not orderable) — OptiSPEED® 900µm Tight Buffered Fiber
 - 460125271 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, multimode
- 860278530 (Product Component—not orderable) — OptiSPEED® LC 0.9 mm Pigtail, slate, 1.5 m
- 760038562 | X-TB-6F-SL-F/G (Product Component—not orderable) — OptiSPEED® 900µm Tight Buffered Fiber
 - 460125271 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, multimode
- 860278548 (Product Component—not orderable) — OptiSPEED® LC 0.9 mm Pigtail, white, 1.5 m
- 760099358 | X-TB-6F-WH-F/G (Product Component—not orderable) — OptiSPEED® 900µm Tight Buffered Fiber
 - 460125271 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, multimode
- 860278555 (Product Component—not orderable) — OptiSPEED® LC 0.9 mm Pigtail, red, 1.5 m
- 760099366 | X-TB-6F-RD-F/G (Product Component—not orderable) — OptiSPEED® 900µm Tight Buffered Fiber
 - 460125271 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, multimode
- 860278563 (Product Component—not orderable) — OptiSPEED® LC 0.9 mm Pigtail, black, 1.5 m
- 760099374 | X-TB-6F-BK-F/G (Product Component—not orderable) — OptiSPEED® 900µm Tight Buffered Fiber
 - 460125271 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm

760031021 | MODG2-12LC-MM-PT

Fiber, multimode

860278571 (Product Component—not orderable) — OptiSPEED® LC 0.9 mm Pigtail, yellow, 1.5 m

- 760099382 | X-TB-6F-YL-F/G (Product Component—not orderable) — OptiSPEED® 900µm Tight Buffered Fiber
- 460125271 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, multimode

860278589 (Product Component—not orderable) — OptiSPEED® LC 0.9 mm Pigtail, violet, 1.5 m

- 760099390 | X-TB-6F-VI-F/G (Product Component—not orderable) — OptiSPEED® 900µm Tight Buffered Fiber
- 460125271 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, multimode

860278597 (Product Component—not orderable) — OptiSPEED® LC 0.9 mm Pigtail, rose, 1.5 m

- 760099408 | X-TB-6F-RS-F/G (Product Component—not orderable) — OptiSPEED® 900µm Tight Buffered Fiber
- 460125271 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, multimode

860278605 (Product Component—not orderable) — OptiSPEED® LC 0.9 mm Pigtail, aqua, 1.5 m

- 760099416 | X-TB-6F-AQ-F/G (Product Component—not orderable) — OptiSPEED® 900µm Tight Buffered Fiber
- 460125271 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, multimode

700206949 | MFA-LC12-BG-SHUTTERED — OptiSPEED® LC Multiport Shuttered Adapter, Beige, Single Pack