

# PANZONE® Horizontal Slack Manager and Accessories

## specifications

The horizontal slack manager shall consist of a steel slack tray and injection molded plastic slack spools and bend radius posts. The horizontal slack manager shall replace a traditional horizontal cable manager and eliminate the need for vertical slack management. Each horizontal slack manager shall be capable of managing 48 Category 6 copper cables or 144 fiber cables. In addition, the horizontal slack manager shall allow the ability to make front-only accessible moves, adds, and changes quickly and easily.

The bend radius post kits shall include two injection molded plastic posts and mounting hardware. The bend radius post kits are zero rack space cable managers that alleviate cable strain when transitioning between the horizontal and vertical channel. The bend radius posts shall have built-in cable retainers that can be oriented or removed by the installer to best manage copper and fiber cables. The bend radius post kits shall be offered in 3 inch, 3.5 inch, and 4 inch increments.



## technical information

### Dimensions:

Part Number	Height In. (mm)	Width In. (mm)	Depth In. (mm)
PZCHSM2	3.5 (89)	19.0 (483)	13.0 (330)
PZBR3	2.7 (70)	0.6 (15)	3.1 (78)
PZBR3.5	2.7 (70)	0.6 (15)	3.6 (91)
PZBR4	2.7 (70)	0.6 (15)	4.1 (103)

<b>Packaging:</b>	<b>PZCHSM2:</b> 2 RU horizontal slack manager, includes six slack spools, four 4" bend radius posts, and assembly hardware
	<b>PZBR3:</b> Two 3" bend radius posts and assembly hardware
	<b>PZBR3.5:</b> Two 3.5" bend radius posts and assembly hardware
	<b>PZBR4:</b> Two 4" bend radius posts and assembly hardware

## key features and benefits

<b>Improved cable routing</b>	Allows the ability to make front accessible moves, adds, and changes quickly and easily
<b>Improved airflow improves side ventilation</b>	Clears the vertical channel of large cable bundles which
<b>Eliminates the need for vertical slack management</b>	Reduces real estate required for rack or cabinet lineups by allowing narrower vertical channels
<b>High capacity horizontal manager</b>	Capable of managing and storing slack for 48 Category 6 copper cables or 144 fiber cables
<b>Zero rack space bend radius posts</b>	Maximizes the number of usable rack spaces for network equipment or patch panels without taking up valuable rack spaces

## applications

The PanZone® Horizontal Slack Manager is an ideal cable management solution for full size cabinets, wall mount cabinets, or racks with limited vertical channel space. The horizontal slack manager is capable of managing and storing slack for 48 Category 6 copper cables or 144 fiber cables. In addition, the horizontal slack manager also helps to improve side ventilation by clearing the vertical channel of large cable bundles. This allows for improved airflow and cooling of network equipment and

is of particular benefit for Power over Ethernet applications. The horizontal slack manager can be installed between an active network switch and patch panel to manage the patch cords, which is especially useful for high-density applications. The PanZone® Bend Radius Post Kits are zero rack space cable managers that alleviate cable strain when transitioning between the horizontal and vertical channel.

### PanZone® Cable Management

<b>2 RU horizontal slack manager:</b>	PZCHSM2
<b>Cable bend radius post, 3":</b>	PZBR3
<b>Cable bend radius post, 3.5":</b>	PZBR3.5
<b>Cable bend radius post, 4":</b>	PZBR4

### PanZone® Wall Mount Cabinets

<b>Perforated door:</b>	PZWMC12P
<b>Window door:</b>	PZWMC12W


### Pan-Net® Racks

<b>2 post rack #12-24 – 8' rack threaded rail:</b>	R2P96
<b>2 post rack #12-24 – 7' rack threaded rail:</b>	R2P
<b>4 post rack #12-24 – 7' rack threaded rail:</b>	R4P
<b>4 post rack 7' with cage nut rail:</b>	R4PCN
<b>4 post rack #12-24 – 8' rack threaded rail:</b>	R4P96
<b>4 post rack 8' with cage nut rail:</b>	R4P96CN


### Net-Access™ Cabinets

<b>45 RU cabinet with side panels, front and rear doors:</b>	N8522B
<b>45 RU cabinet with front and rear doors:</b>	N8529B


# PanZone® Horizontal Slack Manager and Accessories




**PZCHSM2**  
Horizontal Slack Manager, 2 RU  
includes (2) PZBR4 Kits



**PZBR3**  
3" Bend Radius  
Post Kit



**PZBR3.5**  
3.5" Bend Radius  
Post Kit



**PZBR4**  
4" Bend Radius  
Post Kit



**Figure 1: Application of a horizontal  
slack manager and bend radius posts  
installed in a wall mount cabinet**



**Figure 2: Application of a horizontal  
slack manager and bend radius posts  
installed in a full size cabinet**

Dimensions are in inches (Dimensions in parenthesis are in millimeters)

## WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA  
Phone: 800.777.3300

PANDUIT EUROPE LTD.  
London, UK  
cs-emea@panduit.com  
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.  
Republic of Singapore  
cs-ap@panduit.com  
Phone: 65.6305.7575

PANDUIT JAPAN  
Tokyo, Japan  
cs-japan@panduit.com  
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA  
Guadalajara, Mexico  
cs-la@panduit.com  
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.  
Victoria, Australia  
cs-aus@panduit.com  
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to [www.panduit.com/warranty](http://www.panduit.com/warranty)

**For more information**

Visit us at [www.panduit.com](http://www.panduit.com)

Contact Customer Service by email: [cs@panduit.com](mailto:cs@panduit.com)  
or by phone: 800.777.3300

**PANDUIT®**

© 2017 Panduit Corp.  
ALL RIGHTS RESERVED.  
ZCSP23--WW-ENG  
Replaces WW-ZCSP04  
7/2017