

A schematic diagram of a cable structure. It shows multiple parallel strands (represented by thin lines) that are grouped together by a carrier (represented by a thicker line). The strands are labeled "STRAND" and the carrier is labeled "CARRIER".

SE	12	PFR	-	M	R	10	C	SE175___-_R__	(33.7)
							H	SE200P-_R_	1.75 (44.4)
								SE250P-_R_	2.00 (50.8)
									2.50 (63.5)

COLOR 0 : WEATHER RESISTANT BLACK
8 : GRAY
10 : WHITE

REEL

PACKAGE SIZE L : 50 FT (15.24 M)
C : 100 FT (30.48 M)
T : 200 FT (60.96 M)
D : 500 FT (152.4 M)
M : 1000 FT (304.8 M)

MATERIAL P : PET
PFR : FLAME RETARDANT PET

NOM. I.D. SIZE 12 : 0.125 (3.2)
25 : 0.250 (6.4)
38 : 0.375 (9.5)
50 : 0.500 (12.7)
75 : 0.750 (19.1)
125 : 1.250 (31.8)
150 : 1.500 (38.1)
175 : 1.750 (44.5)
200 : 2.000 (50.8)
250 : 2.500 (63.5)

1. ALL STRANDS OF THE PET SLEEVING SHALL BE THE SAME COLOR.
2. THE FLAME RETARDANT PET MATERIAL SHALL HAVE ALL STRANDS THE SAME COLOR EXCEPT FOR TWO CRISSCROSS WHITE TRACERS(EACH TRACER CONSISTING OF ONE COMPLETE CARRIER)-OR-ONE SINGLE STRAND TRACER(ONE STRAND WITHIN CARRIER IS THE OPPOSITE COLOR).ALL STRANDS OF WHICH ARE WHITE, EXCEPT FOR WHITE SLEEVING, THE TRACERS ARE THEN BLACK.

E



DIMENSIONS IN BRACKETS ARE METRIC [mm]

G03597BX_DC_GB0239KD/00F

PANDUIT

STANDARD BRAIDED
EXPANDABLE SLEEVING (SE)
(CUSTOMER DRAWING)

B

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES. THIRD ANGLE PROJECTION.

[illegible]

GB0239KD

A
SIZE

OOF	3-27-12	LEF	VJS	H: RE-ADDED PANDUIT PART NUMBERS SE200P&SE250P G: ADDED "CUSTOMER DRAWING" TO TITLE DESCRIPTION F: ADDED NOTE #3, #4 AND TABLE.	GB0239KD	OOF	RAM I	
OOE	12-19-11	LEF	VJS	E: REMOVED NOTE #3 FROM NOTES. D: REMOVE COLOR "C" CLEAR C: REMOVE PARTS SE200P-R AND SE250P-R B: REPLACE TOLERANCING WITH N/A A: MATERIAL CHANGED TO PART# DESCRIPTION	GB0239KD	OOE	RAM I	
OOD	10-11-09	TMSA		CHANGED UPPER BUNDLE DIAMETER FOR THE FOLLOWING SE38 FROM .625 , SE150 FROM 2.250, & SE250 FROM 4.500 REMOVED NOTE 3 AND RENUMBERED NOTES.	GB0239KD	OOC		
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	