

**NEW!**  
more on  
reverse

# Versatile Pole-Mount Box

*For Outdoor Security Camera, Electrical Accessories Installations*



8161PM...the easy way to mount security cameras, detectors and more, outside on a rigid pipe.

**NEW!**

Arlington's new **POLE-MOUNT Box** features an integral mounting bracket. Now you can install a camera, or other electrical accessory anywhere you need to on a rigid pipe 3" to 6" in diameter. Fast and easy to install, the new **8161PM** box attaches to a round metallic or non-metallic pole with hose clamps.

**8161series boxes** offer flexible solutions to mounting security cameras, detectors, electrical accessories or fixtures outdoors!

These non-metallic boxes hold up to 50 lbs in most applications; 10 lbs on a wall. They have positionable threaded openings so you can install a camera (etc) where you need it now; then install additional cameras later.

You can install a power or low voltage camera (with mounting holes wider than 4.5" apart) right on the box and mount it in a variety of ways to a wall or ceiling. In addition to the new **POLE-MOUNT Box**:

- Wall, soffit or eave-mount (8161TR)
- Face-down, wall-mount (8161BR)
- Face-down corner-mount (8161CB)
- Mounting on a down rod (8161BP)
- Non-metallic, UV rated for long outdoor life
- For interior or exterior use in dry, damp or wet locations

*See all 8161 series products on back.*

**A**  
**Arlington**

1 Stauffer Industrial Park  
Scranton, PA 18517  
**800/233.4717**  
**Fax 570/562.0646**  
**www.aifittings.com**



Catalog Number	UPC/DEI/NAED Mfg. #018997	Description	Weight Rating /Mounting	Unit Pkg	Std Pkg
<b>8161PM</b>	09020	Pole-mount Box	50 lb/pole	1	10
<b>8161PMGC</b>	09021	Pole-mount Box, w/ ground clip	50 lb/pole	1	10

Features integral mounting bracket (hose clamps not included).  
Fits rigid pipe, 3 to 6 inches in diameter.

# Versatile 8161 series...Installation Options

*Mounts Cameras, Fixtures, Detectors up to 50 lbs, Inside or Out*


## 8161 series

- Mounts security cameras, electrical accessories and fixtures indoors or outside
- Screw pattern matches standard 4" fixture box
- Box includes 3/4" to 1/2" reducing bushing
- UV rated for long outdoor life in dry, damp or wet locations
- Available with grounding clip for use in Canada



## 8161TR

**Wall or ceiling mount**  
up to 10 lbs on wall;  
50 lbs on ceiling



## 8161BR

**Wall-mount**  
up to 50 lbs  
facing down

8161BR  
Includes sturdy, built-in wall mount bracket, mounting screws



## 8161BP

**Pipe-mount**  
up to 50 lbs  
facing down  
on a down rod



8161BP  
Includes installed threaded base plate (support pipe not included)



## 8161CB

**Corner-mount**  
up to 50 lbs



8161CB  
Includes integral corner mount bracket



Patents pending



View 8161 Video



**Arlington**

1 Stauffer Industrial Park  
Scranton, PA 18517

**800/233.4717**

**Fax 570/562.0646**

**www.aifittings.com**



Catalog Number	UPC/DEI/NAED Mfg. #018997	Description Plastic 1-piece Box w/ Threaded Openings	Weight Rating /Mounting	Unit Pkg	Std Pkg
8161TR	00878	Box w/ threaded openings	50 lb/ceiling; 10 lb/wall	1	10
8161TRGC	08942	Box w/ threaded openings, w/ ground clip	50 lb/ceiling; 10 lb/wall	1	10
8161BR	08881	Box w/ built-in bracket	50 lb/wall	1	10
8161BRGC	08883	Box w/ built-in bracket, w/ ground clip	50 lb/wall	1	10
8161BP	08880	Box w/ built-in base plate	50 lb/down rod	1	10
8161BPGC	08882	Box w/ built-in base plate, w/ ground clip	50 lb/down rod	1	10
8161CB	01530	Box w/ corner-mount bracket	50 lb/corner	1	10
8161CBGC	11300	Box w/ corner-mount bracket, w/ ground clip	50 lb/corner	1	10

**SC5 CAM-KIT™** 18058 Plastic camera mounting kit (base dia. UNDER 4.5")

1 20

**Camera mounting OPTION** for cameras with base diameter of less than 4.5"  
Includes 5" round plastic mounting plate, camera mounting bracket, mounting screws.

Distributed by