



ORTRONICS®

WHITE CLARITY™ PATCH PANELS

Legrand's® new offering of white Clarity™ patch panels is now available with our popular 6-port connector versions as well as our High Density Jack (HDJ) versions. These new panels compliment and support the growing interest in Legrand's white racks and cabinets. This initial white panel offering targets our most popular panel constructions with both flat and angled versions.

FEATURES:

- Available in Clarity 6A, 6 and 5E performance
- Available in angled or flat, 1RU and 2RU versions
- 6-port or HDJ terminations
- Elements of nCompass™ + channel solutions
- RoHS compliant and UL listed to UL1863
- Have published Product Environmental Profiles (PEPs)

BENEFITS:

- Support any premium performance application
- Variety of cable management and port presentation options
- Multi-port 110 termination or individual jack options
- Elevated channel performance with margin over standards performance
- Code compliant
- Sustainable product documentation

designed to be better.™

 **legrand**®

WHITE CLARITY PATCH PANELS

WHITE CLARITY® PANELS WITH 6-PORT CONNECTOR MODULES

PART NO.	DESCRIPTION
OR-PHA6AU24-W	24-port, angled panel, Clarity 6A, 1.75" x 19", white
OR-PHA6AU48-W	48-port, angled panel, Clarity 6A, 3.5" x 19", white
OR-PHD6AU24-W	24-port, flat panel, Clarity 6A, 1.75" x 19", white
OR-PHD6AU48-W	48-port, flat panel, Clarity 6A, 3.5" x 19", white
OR-PHA66U24-W	24-port, angled panel, Clarity 6, 1.75" x 19", white
OR-PHA66U48-W	48-port, angled panel, Clarity 6, 3.5" x 19", white
OR-PHD66U24-W	24-port, flat panel, Clarity 6, 1.75" x 19", white
OR-PHD66U48-W	48-port, flat panel, Clarity 6, 3.5" x 19", white
OR-PHA5E6U24-W	24-port, angled panel, Clarity 5E, 1.75" x 19", white
OR-PHA5E6U48-W	48-port, angled panel, Clarity 5E, 3.5" x 19", white
OR-PHD5E6U24-W	24-port, flat panel, Clarity 5E, 1.75" x 19", white
OR-PHD5E6U48-W	48-port, flat panel, Clarity 5E, 3.5" x 19", white



PHA6AU24-W



OR-PHD66U48-W



OR-PSAHJU48-W



OR-PSDHJU48-W



OR-HDJ6A-88 OR-HDJ6-88 OR-HDJ5E-88

WHITE UNLOADED HDJ PANELS

OR-PHAHJU24-W	24-port, angled, unloaded, HDJ panels, 1.75" x 19", white
OR-PSAHJU48-W	48-port, angled, unloaded, HDJ panels, 3.5" x 19", white
OR-PHAHJU72-W	72-port, angled, unloaded, HDJ panels, 3.5" x 19", white
OR-PHDHJU24-W	24-port, flat, unloaded, HDJ panels, 1.75" x 19", white
OR-PSDHJU48-W	48-port, flat, unloaded, HDJ panels, 3.5" x 19", white
OR-PHDHJU72-W	72-port, flat, unloaded, HDJ panels, 3.5" x 19", white

HIGH DENSITY JACKS

OR-HDJ6A-88	Clarity HDJ Category 6A jack, with lacing cap termination, white
OR-HDJ6-88	Clarity HDJ Category 6 jack, with lacing cap termination, white
OR-HDJ5E-88	Clarity HDJ Category 5E jack, with lacing cap termination, white



designed to be better.™

