

# ToughLED™ High Output 5ft

## High output LED weatherproof

- Up to 30% energy saving against linear fluorescent
- Instant start, flicker free
- Polycarbonate diffuser and body, suitable for food preparation areas
- Stainless steel anti-tamper clips
- Quick and easy point for point installation



Code	Description	Col temp.	Dim.	Watt	Lumens	LpcW
JC71501	ToughLED 5ft single	4000K	No	49W	4500	92
JC71501DALI**	ToughLED 5ft single DALI	4000K	Yes	49W	4500	92
JC71501DSI**	ToughLED 5ft single DSI	4000K	Yes	49W	4500	92
JC71501/1-10V	ToughLED 5ft single 1-10V	4000K	Yes	49W	4500	92
JC71509**	ToughLED 5ft single microwave on/off	4000K	No	49W	4500	92
JC71509SD**	ToughLED 5ft single microwave step dim	4000K	-	49W	4500	92
JC71505**	ToughLED 5ft single emergency	4000K	No	49W	4500	92
JC71505DALI**	ToughLED 5ft single emergency DALI	4000K	Yes	49W	4500	92
JC71505DSI**	ToughLED 5ft single emergency DSI	4000K	Yes	49W	4500	92
JC71505/1-10V**	ToughLED 5ft single emergency 1-10V	4000K	Yes	49W	4500	92
JC71503	ToughLED 5ft twin	4000K	No	98W	9000	92
JC71503DALI**	ToughLED 5ft twin DALI	4000K	Yes	98W	9000	92
JC71503DSI**	ToughLED 5ft twin DSI	4000K	Yes	98W	9000	92
JC71503/1-10V**	ToughLED 5ft twin 1-10V	4000K	Yes	98W	9000	92
JC71511**	ToughLED 5ft twin microwave on/off	4000K	No	98W	9000	92
JC71511SD**	ToughLED 5ft twin microwave step dim	4000K	-	98W	9000	92
JC71507**	ToughLED 5ft twin emergency	4000K	No	98W	9000	92
JC71507DALI**	ToughLED 5ft twin emergency DALI	4000K	Yes	98W	9000	92
JC71507DSI**	ToughLED 5ft twin emergency DSI	4000K	Yes	98W	9000	92
JC71507/1-10V**	ToughLED 5ft twin emergency 1-10V	4000K	Yes	98W	9000	92
JC71525	ToughLED 1.5m suspension kit (single)	-	-	-	-	-
JC71526	ToughLED 1.5m suspension kit (twin)	-	-	-	-	-

\*Requires online registration.

**NEW** New product for 2018

5 year ext. warranty\*

Dimmable options available

Sensing options available

Emergency options available

### Classification

⚡ Class 1\*\*

📦 Class 2

IP65 | 240V

IK09 impact rating

### LED

4000K | CRI: Ra (80)

### Finishes

Grey

### Construction


Body: Polycarbonate

Diffuser: Polycarbonate

### Accessories

1.5m Suspension kit - Single (JC71525), Twin (JC71526)

JC71501 JC71503



All data sheets and installation sheets available at [jcc.co.uk](http://jcc.co.uk)