
CLARITY 5E ANGLED 24-PORT PANEL, CAT 5E, SIX-PORT MODULES, 19" X 1.75"

OR-PHA5E6U24 | [Ortronics](#)



FEATURES & BENEFITS

Clarity 5E angled 24-port high density patch panel is component compliant to TIA/EIA Category 5e performance requirements. It occupies 1 rack unit and measures 19" x 1.75". Jacks are grouped in six-port modules. It is part of the Clarity 5E link and channel solution that provides significant installed performance headroom.



PRODUCT
ENVIRONMENTAL PROFILE

- **Recessed design with lower mounted profile:** Directs cords more easily to vertical management.
- **ETL verified to TIA Category 5e component spec:** Elevated component performance.
- **Center tuned to Clarity 5E patch cords:** More transparent mated union.
- **Universal wiring:** Supports T568A and T568B installs.
- **Easy lace 110 termination:** Saves installation time.
- **Supplied rear cable management:** Supports good cabling practice.
- **High density design:** Maximizes rack utilization.
- **RoHS compliant:** Lead free.

SPECIFICATIONS

GENERAL INFO

Mod Jack Wiring: Universal T568A/B
Number Of Ports: 24
Performance Category: Cat 5e component compliant
Product Series: Clarity
Type: Patch Panels

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CUL Listing No: E131600
ETL Listing No: 3013270-004
UL Listing No: E131600

CONSTRUCTION INFORMATION

Component 1: Panel

Component 2: Six-port jack housing

Component 3: Six-port rear IDC housing

Component 4: Array of eight modular dual reactance contacts

Component 5: IDC contacts (low noise)

Finish Plating 1: Painted black - texture with green silkscreen

Finish Plating 4: Nickel plating and a minimum of 50 micro inches of selective gold plating in contact area

Finish Plating 5: Nickel plating with tin over plate

Material 1: .090" Aluminum

Material 2: High impact thermoplastic UL 94V-0

Material 3: Polycarbonate

Material 4: Beryllium copper

Material 5: Phosphor Bronze

DIMENSIONS

Cable Diameter Range: 22-26 AWG

Depth (Metric): 46.23 mm

Height (Metric): 44.45 mm

Height (US): 1.75"

Width (Metric): 482.6 mm

TECHNICAL INFORMATION

Category Rating: Cat 5e component compliant

Performance Rating: Cat5e

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

