

Jabra Evolve 20 and Evolve 20SE

Professional headset with easy call management to enhance productivity in the open office

- Great sound for calls and music
- Manage calls easily
- Flexible Plug and Play connectivity



Jabra Evolve 20

Jabra Evolve 20 Special Edition

Detail	Information
Packaging dimensions	L 23 x W 18 x H 3.5cm (7.09 x 9.06 x 1.38 in)
Weight mono / stereo	Evolve 20: 0.1425kg / 0.1711kg. Evolve 20SE: 0.1443kg / 0.1747kg
Whats in the box	Jabra Evolve 20/20SE Headset, Warning leaflet, Warranty leaflet, Quick start guide, USB Controller, Plastic bag for controller, Plastic bag for headset, Certified for Skype for Business sticker (Refer to BOM), Foam bag for the left earcup of the Stereo headset only, Evolve 20 with foam ear cushions/Evolve 20SE with leatherette ear cushions.
Battery included	No
AC power supply	USB power supply by PC
Certifications	Regulatory Approvals: CE, FCC, KCC, RCM, UL, Industrial Certifications: MS Lync, Avaya, Cisco
Warranty	2 years
Bluetooth® device	No
DECT Device	No
NFC	No
Headset bandwidth	Wideband
Connection (mini jack, USB, etc)	USB
Speaker Size	D 28x3.9mm
Speaker sensitivity	93.6dB SPL @1kHz
Speaker impedance	32+/-4.8, @1.0kHz
Speaker Max Input Power	Rated Input 5mW @0.4V, max input 10mW @0.56V
Speaker Frequency Range	150Hz~7kHz, @Output S.P.L -10dB
Microphone type	Electret Condenser Microphone
Microphone Sensitivity	F=1kHz, Pin=1Pa, 0dB=1V/Pa, Min=-48dB, Max=-44dB
Microphone Frequency Range	100Hz ~ 10kHz @6dB
Speaker bandwidth Music mode	Wideband
Speaker bandwidth Speak mode	Wideband
Microphone bandwidth	Wideband
Cord length	Control cable: 95cm, HS cable: 120cm
Operating temperature	-10 °C to + 50 °C
Storage temperature	-30 °C to + 80 °C Storage temperature range: (-20°C to +35°C 6 months), (+35°C to +45°C 3 months), (+45°C to +45°C 1 month), (+60°C to +70°C 1 hour with no degradation), (+70°C to +85°C max. 1 hour (<20% degradation)
Power consumption speaker	Rated Input 5mW @0.4V, max input 10mW @0.56V
Features	HD Voice, PeakStop™ technology, UC plug-and-play, noise canceling microphone, HiFi sound, remote call control/easy call management, Jabra software compatible, crystal clear sound, on the ear wearing style, passive noise cancellation

* Phone dependent

Jabra Evolve 20

SKU	Description	EAN Code
4999-823-109	Jabra Evolve 20 MS Stereo	5706991016970
4999-829-209	Jabra Evolve 20 UC Stereo	5706991016987
4993-823-109	Jabra Evolve 20 MS Mono	5706991016994
4993-829-209	Jabra Evolve 20 UC Mono	5706991017007

Jabra Evolve 20SE

SKU	Description	EAN Code
4999-823-309	Jabra Evolve 20SE MS Stereo	5706991021158
4999-829-409	Jabra Evolve 20SE UC Stereo	5706991021134
4993-823-309	Jabra Evolve 20SE MS Mono	5706991021141
4993-829-409	Jabra Evolve 20SE UC Mono	5706991021127

Jabra.com/evolve20