

Keystone 80mm X 80mm Faceplates

specifications

80mm X 80mm faceplate shall include a 2-port sloped shuttered adapter to protect connections from dust and debris when not in use. Faceplate shall include a label pocket with a hinged label cover and label to ensure proper identification. Two piece design includes a metal mounting plate that shall be concealed by the outer frame for added security and aesthetic look. Faceplate shall accept standard Keystone modules for copper, fiber and audio/video installations



80mm X 80mm Faceplates

White: KFPL80S2SWH

Shielded Jack Module

Jack Module: KJS6X88TC

technical information

Mounting options:	Mounting plate compatible with DIN openings
Number of ports:	2-port configuration; sloped and shuttered
Packaging:	Includes mounting plate, plastic frame, 2-port 50mm X 50mm shuttered adapter, label, and hinged label cover
Material:	Cover and adapter are made of ABS material The mounting plate is zinc die-cast

key features and benefits

Modular	Keystone modules snap in and out for easy moves, adds and changes
Sloped ports	45° ports facilitate cable flow and provide more cable room
Concealed screws	Utilizes two-piece design that allows the frame to mount over the base to hide the mounting screws for added security and aesthetics
Labeling capability	Includes label pocket that allow ports to be properly identified
Hinged doors	Protect connections from dust and debris


applications

Panduit Keystone Faceplates offer an aesthetic solution that complements work areas, while offering various features that enhance functionality by offering modularity and flexibility. Will support copper, fiber and audio/video applications. As part of a global workstation outlet solution offered by Panduit, Keystone 80mm X 80mm Faceplates mount to select industry-standard wall boxes as a two piece design that provides a mounting plate to secure jacks to wall box and a frame

that will conceal the mounting method. Two port 50mm X 50mm adapter will screw directly to the mounting plate through the label pocket, securing all the components in place. Adapter includes shuttered doors that can be closed manually when connections are not in use to protect them from dust and debris. Built-in label pocket includes a hinged cover that remains attached to the faceplate while labeling to avoid misplacing.

Keystone 80mm X 80mm Faceplates

80mm Faceplate Frame



Dimensions are in inches. [Dimensions in brackets are metric].

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com/ia

iai@panduit.com

PANDUIT[®]

©2018 Panduit Corp.
ALL RIGHTS RESERVED.
COSP455--WW-ENG
10/2018