



GREENLEE®
COMMUNICATIONS
A Textron Company

Tele-Mate® Pro Telephone Test Sets

TM-700, TM-700T, TM-700i and TM-700UK



Easy to Use, DSL Compatible, Smart Telephone Test Set.

For the evolving world of telecommunications, Greenlee Communications is proud to introduce the **NEW Tele-Mate® Pro TM-700 Telephone Test Set.**

The TM-700 helps technicians install, service, and maintain voice services with ease. DSL compatible in both Monitor and Talk modes, the TM-700's LCD screen makes reading polarity, voltage, current, and ringing frequencies easier than ever, and clearly shows speed dials and recent numbers for faster access.

The TM-700 features over-voltage and over-current detection for safer operation and also features an intercom mode, a built in toner for pair tracing, and DTMF detection and measurement for enhanced productivity. Use the built in loudspeaker or with a headset (included) for easy hands free operation.

The Greenlee Communications TM-700 makes your job faster, safer, and easier.

www.greenlee.com

Features

- LCD for easy dialing, programming, caller ID, voltage, current, ringing, and DTMF measurements
- Safe over voltage and over current protection
- Intercom for "dead-pair" talking
- SmartIntercom™ between Tele-Mate® Pros (including PE830); allows "ringing" the far end
- Tone generator for pair identification
- Luminescent (glow-in-the-dark) keypad
- DSL line filter
- Super Impedance Amplifier to monitor lines without disrupting traffic
- Tone and Pulse dialing for old and new phone lines with Pause and Flash (TBR)
- User options allow USA or ETSI telephony with individual options available
- RJ11 socket for easy cord changes
- Ten last number redial & ten number speed dial memories
- Headset (included) for hands free operation, with loudspeaker option
- Volume control & mute
- Requires just two AA cells, readily available and low cost

Specifications

TECHNICAL SPECIFICATIONS	
Length:	9.25" (235 mm)
Width:	2.5" (64 mm)
Height:	3.25" (83 mm)

Ordering Information

CAT NO.	UPC NO.	DESCRIPTION	QTY.
TM-700	00984	TM-700 Test Set with ABN "Bed-Of-Nails" Croc Clips & RJ11 (POS)	1
TM-700T	00983	TM-700 Test Set with ABN "Bed-Of-Nails" Croc Clips & RJ11 (Boxed)	1
TM-700i	00977	TM-700 Test Set with Small Croc Clips (Boxed)	1
TM-700UK	00978	TM-700 Test Set with BT Plug (Boxed)	1

NOTE 1: The TM-700i contains standard, small croc clips that do not pierce wiring. ABN style clips are also known as "bed of nails" since they pierce the wiring for testing.

NOTE 2: The TM-700 (POS – point of sale, with full color "oversleeve") replaces the PE-830. The PE-830 is discontinued.

DISTRIBUTOR INFORMATION:

