




**Color:**  Black

**UPC Code:** 078477843253

**Country Of Origin:** Mexico

**NEMA:**  
14-60R



## 9460

60 Amp, 125/250 Volt, NEMA 14-60R, 3P, 4W, Flush Mtg Receptacle, Straight Blade, Industrial Grade, Grounding, , Side Wired, Steel Strap, - Black

Leviton's line of Extra Heavy-Duty Industrial Grade receptacles are designed and manufactured to withstand the harsh conditions typically associated with industrial environments. Available in a wide variety of configurations, including isolated ground, tamper-resistant, hospital grade, etc., these Industrial Grade devices are the electrical contractor's choice for use in factories, schools, hospitals and commercial office buildings.

### Technical Information

AC Horsepower Ratings

**At Rated Voltage:** 3-1/2 HP

Electrical Specifications

**Amperage:** 60 A

**Current Limiting:** Full Rated Current

**Dielectric Voltage:** Withstands 2000V per UL498

**Grounding:** Grounding

**Pole:** 3

**Temperature Rise:** Max 30C after 50 cycles OL at 150 percent rated current

**Voltage:** 125/250 VAC

**Wire:** 4

Environmental Specifications

**Operating Temperature:** -40°C to 60°C

Material Specifications

**Body Material:** Nylon

**Color:** Black

**Face Material:** Nylon

**Line Contacts:** Brass Double-Wipe

**Strap Material:** Galvanized Steel

Mechanical Specifications

**Product ID:** Ratings are permanently marked on device

**Terminal Accom.:** Up to 4 AWG

**Terminal ID:** Brass-Hot, Green-Ground, Silver-Neutral

Product Features

**Color:** Black

**Device Type:** Power Device

**NEMA:** 14-60R

Standards and Certifications

**ANSI:** C-73


**CSA C22.2 No. 42:** File 152105

**NEMA:** WD-6


**NOM:** 057

**UL498:** File E13399

**Warranty:** 10 Year Limited



### Wiring Diagram



### SPECIFICATION SUBMITTAL

JOB NAME:	CATALOG NUMBERS:	
<input type="text"/>	<input type="text"/>	<input type="text"/>
JOB NUMBER:	<input type="text"/>	<input type="text"/>

#### Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday):

+1-800-824-3005

#### Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · [www.leviton.com/canada](http://www.leviton.com/canada)

#### Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-

1797 · [www.leviton.com.mx](http://www.leviton.com.mx)

Visit our Website at: [www.leviton.com](http://www.leviton.com)

© 2018 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

#### Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

[www.leviton.com/international/contacts/](http://www.leviton.com/international/contacts/)

