





Product updated on April 03, 2018

## Blister Packed Enhanced Pigtaileds



We now can offer you a more convenient and cost effective way to purchase enhanced pigtaileds. You get the usual high quality pigtaileds but now with a reduction in the amount of packaging and paperwork, saving costly engineers time unpacking on-site.

### FEATURES/BENEFITS

- Blister packed pigtaileds include FC, LC, SC & ST variations
- Easy strip 900 µm buffer as standard - Tight bufer available on request
- IEC and DIN color codes available (IEC as Standard)
- Convenient space saving shipping & storage
- Blister pack offers superior transport protection
- Environmentally friendly, generating less waste from packaging and certification

SPECIFICATIONS

Connector Performance

	MAX
Insertion Loss	$\leq 0.25$ B
Return Loss (SM UPC)	$\geq 55$ B
Return Loss (SM APC)	$\geq 65$ B
Operating Temperature	-20°C to + 60°C
Intermateability	Compatible with all equivalent connectors as per IEC 61754

## ORDERING INFORMATION

DESCRIPTION	PART NUMBER
Pack of 12 SC/UPC Pigtail 1.5mtr Easy Strip - 9/125 900 µm (12 Colours) Blister Packed	SC09B1.5BP12
Pack of 12 SC Pigtail 1.5mtr Easy Strip - 62.5/125 900 µm (12 Colours) Blister Packed	SC62B1.5BP12
Pack of 12 SC Pigtail 1.5mtr Easy Strip - 50/125 900 µm (12 Colours) Blister Packed	SC50B1.5BP12
Pack of 12 SC Pigtail 1.5mtr Easy Strip - OM3 900 µm (12 Colours) Blister Packed	SCOM3B1.5BP12
Pack of 12 ST/UPC Pigtail 1.5mtr Easy Strip- 9/125 900 µm (12 Colours) Blister Packed	ST09B1.5BP12
Pack of 12 ST Pigtail 1.5mtr Easy Strip - 62.5/125 900 µm (12 Colours) Blister Packed	ST62B1.5BP12
Pack of 12 ST Pigtail 1.5mtr Easy Strip - 50/125 900 µm (12 Colours) Blister Packed	ST50B1.5BP12
Pack of 12 ST Pigtail 1.5mtr Easy Strip - OM3 900 µm (12 Colours) Blister Packed	STOM3B1.5BP12
Pack of 12 FC/UPC Pigtail 1.5mtr Easy Strip - 9/125 900 µm (12 Colours) Blister Packed	FC09B1.5BP12
Pack of 12 FC Pigtail 1.5mtr Easy Strip - 62.5/125 900 µm (12 Colours) Blister Packed	FC62B1.5BP12
Pack of 12 FC Pigtail 1.5mtr Easy Strip - 50/125 900 µm (12 Colours) Blister Packed	FC50B1.5BP12
Pack of 12 FC Pigtail 1.5mtr Easy Strip - OM3 900um (12 Colours) Blister Packed	FCOM3B1.5BP12
Pack of 12 LC/UPC Pigtail 1.5mtr Easy Strip - 9/125 900um (12 Colours) Blister Packed	LC09B1.5BP12
Pack of 12 LC Pigtail 1.5mtr Easy Strip - 62.5/125 900um (12 Colours) Blister Packed	LC62B1.5BP12
Pack of 12 LC Pigtail 1.5mtr Easy Strip - 50/125 900um (12 Colours) Blister Packed	LC50B1.5BP12
Pack of 12 LC Pigtail 1.5mtr Easy Strip - OM3 900um (12 Colours) Blister Packed	LCOM3B1.5BP12



## FURTHER INFORMATION

- For additional information please contact your sales representative
- To view the product 360 visit the product page (Scan the QR code or visit the link below)
- Downloaded from <https://www.aflhyperscale.com/product/blister-packed-enhanced-pigtails>
- AFL Hyperscale reserves the right to make changes in this datasheet at any time without notice
- Information in this document is correct as of April 03, 2018

SCAN QR FOR PRODUCT PAGE

## Europe

+44 (0) 1908 441 144  
emeasales@aflhyperscale.com  
© AFL Hyperscale 2018

## Americas

+1 800 790 9932  
usasales@aflhyperscale.com

## Middle East &amp; Africa

+971 4 404 9606  
mesales@aflhyperscale.com

## India

+91 80 46874687  
indiasales@aflhyperscale.com

## Asia Pacific

+86 755 2561 3694  
apacsales@aflhyperscale.com