

## Component Video with Stereo Audio over Cat5/Cat6 Extender Kit, Wallplate Transmitter and Receiver, Up to 700-ft.

MODEL NUMBER: **B136-101-WP-1**



Is your TV or other display far away from your audio/video source? This wallplate kit allows a TV, projector, etc. with component video input to be placed up to 300 ft. away from a component audio/video source using ordinary Cat5e UTP cabling. It's great for presentation/conference rooms at a great price!

### Description

Tripp Lite's B136-101-WP-1 Cat5 Extender Wallplate Kit with Component Video + Stereo Audio comes with both local and remote wallplates, allowing you to place a TV, Projector, etc up to 300 ft. away from the source. A 1080i (60Hz) Component Video and Stereo Audio signal can be extended up to 300 ft. when using 24Awg, Solid Wire UTP cable (Tripp Lite N022-01K-GY or N222-01K-GY); or up to 400 ft. when using Zero-Skew UTP cable (Tripp Lite P524-01K). A 480p (60Hz) Component Video and Stereo Audio signal can be extended up to 500 ft. when using 24Awg, Solid Wire UTP cable (Tripp Lite N022-01K-GY or N222-01K-GY); or up to 700 ft. when using Zero-Skew UTP cable (Tripp Lite P524-01K). Simple RJ45 Jack connection on the back of the wallplates. No external power required.

### Features

- Comes with both local and remote wallplates
- Easy RJ45 rear connection jacks on both wallplates
- A 1080i (60Hz) Component Video and Stereo Audio signal can be extended up to 300 ft. when using 24Awg, Solid Wire UTP cable (Tripp Lite N022-01K-GY or N222-01K-GY); or, up to 400 ft. when using Zero-Skew UTP cable (Tripp Lite P524-01K)
- No external power required

## Specifications

### Highlights

- Extends a 1080i (60Hz) Component Video and Stereo Audio signal up to 300 ft.
- No external power required

### Package Includes

- B136-101-WP-1 Cat5 Extender Wallplate Kit with Component Video + Stereo Audio ( 2 pieces )
- Wallplate Mounting Screws
- Owner's Manual



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

OVERVIEW	
UPC Code	037332162878
PHYSICAL	
Color	White
Shipping Dimensions (hwd / cm)	4.32 x 20.07 x 13.97
Shipping Dimensions (hwd / in.)	1.70 x 7.90 x 5.50
Shipping Weight (kg)	0.32
Shipping Weight (lbs.)	0.70
COMMUNICATIONS	
Max 1024 x 768 Range (ft)	700
Max 480P Range (ft)	700
Max 1440 x 900 Range (ft)	400
Max 1080i Range (ft)	400
Max 480i Range (ft)	700
Max 640 x 480 Range (ft)	700
Max 800 x 600 Range (ft)	700
Max 1600 x 1200 Range (ft)	400
Max 720P Range (ft)	400
CONNECTIONS	
Ports	1
Side A - Connector 1	(5) RCA (FEMALE)
Side A - Connector 2	RJ45 (FEMALE)
Side B - Connector 1	(5) RCA (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
FEATURES & SPECIFICATIONS	
Technology	Component; Stereo Audio
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

<https://www.tripplite.com/products/product-certification-agencies>